



LZ2S54233 - LZ2S Series, Stainless Steel 54 W Fluorescent Light Fixture (Two 4-Foot Lamps Not Included), Double-Ended Lamp Type, 347-480V, Hub 3/4"

By Killark
Catalog # [LZ2S54233](#)



LZ2S Series - Stainless Steel 54 Watt Fluorescent Light Fixture (Two 4-Foot Lamps Not Included) - Double-Ended Lamp Type - 347-480V - Hubsizes 3/4 Inch NPT

Features

- NEMA 4X & IP66 rated stainless enclosure with Lexan® impact resistant polycarbonate lens.
- Two 3/4" NPT stainless hubs - one at each end (includes aluminum 3/4" close- up plug and two 3/4" x 1/2" reducers for maximum user flexibility).
- Two 1/4" - 20 stainless bushings furnished in top of fixture for threaded rod.

General

Catalog Number	LZ2S54233
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Lamp Type	T5
Light Source	Linear Fluorescent
Material	Polyester, Fiberglass Reinforced
Mounting Type	<ul style="list-style-type: none">• Pendant• Surface
Number of Lamps	0
Optic Type	Polycarbonate Lens - Clear
Reflector Type	Steel Reflector
Series	LZ2S
Type	Stainless Steel Fluorescent Fixture
UPC	783936094335

Dimensions

Dimensions	4.5 in x 1 in x 6.5 in
Gross Weight with Packaging	23

Height	6.5 in
Length	4.5 in
Width	1 in

Electrical Ratings

Amperage Rating	0.35 A
Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	54 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

- [Certifications - LZ2S Series CSA Cert](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_LZ2N Series Fluorescent Luminaires IOM_K1267](#)
- [Photometry - KIL_LZ2x543](#)
- [Specifications - LZ Series Fluorescent Fixtures Specification Sheet](#)
- [Specifications - LZ2S54233 Specification Sheet English](#)
- [Specifications - LZ2S54233 Specification Sheet French](#)
- [Specifications - LZ2S Series Fluorescent Fixtures Specification Sheet](#)