



NVSLCFG25AAG - NV2 Series, Gray Non-Metallic Cmpct Flashing LED Lt Fixt (w/ LED), 3/4" Pendant Mount w/ Amber Strobelight & Guard, 120-240VAC, 50/60Hz

By Killark

Catalog # [NVSLCFG25AAG](#)

NV2 Series - Gray Non-Metallic Corrosion Resistant Compact Flashing LED Light Fixture (LED Included) - 3/4 Inch Pendant Mount With Amber Strobelight And Guard - 120-240VAC At 50/60Hz



Features

- NVSL Series LED with very compact profile and 50,000 hours expected life steady - on or flashing.
- NVSZ Series Xenon with 10,000 hours expected life flashing only.
- LED utilizes inverted cone design to provide full 360 degree coverage for more light projection.
- LED and Xenon available in five colors colors - red, green, amber, blue and clear.
- Flash rate for LED is 7 micro flashes approximately every second for increased visual perception.
- Xenon flash rate 60 to 80 per minute
- Can be mounted in any orientation including lens in the UP or SIDE positions.
- Materials: High strength 30% glass-filled thermoset polyester body with Lexan® lens. Resists corrosive effects of most chemicals, hydrocarbons and solvents
- Designed for indoor and outdoor applications

General

Catalog Number	NVSLCFG25AAG
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Steady
Material	Polyester, Fiberglass Reinforced
Optic Type	Polycarbonate Globe - Amber
Series	NV
UPC	783936070315

Dimensions

Diameter - Inside	2.19 in
Dimensions	5.5 in x 17.5 in x 5.5 in
Gross Weight with Packaging	1.85
Height	5.5 in

Hub Size	3/4"
Length	5.5 in
Width	17.5 in

Electrical Ratings

Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 6A BREAKING @ 120 VAC; 3A BREAKING @ 240 VAC; 1.5A BREAKING @ 480 VAC; 1.2A BREAKING @ 600 VAC; 10A CARRYING @ 120 VAC; 10A CARRYING @ 240 VAC; 10A CARRYING @ 480 VAC;
Frequency Rating	50/60 Hz
Voltage Rating	120-240 VAC

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Division 2, Groups F, G• Class III, Divisions 1 & 2
IP Rating	IP66

Product Assets

- [Certifications - NVSL & NVSP Series CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - NVSLCFG25AAG Specification Sheet French](#)
- [Specifications - NVS Series Non-Metallic Corrosive Resitant Signals Specification Sheet](#)
- [Specifications - NVSLCFG25AAG Specification Sheet English](#)

