



VM1L5030 - VM1L LED Low Bay, Hazardous Rated 50W 5000K, 7656 Lumens

By Killark
Catalog # [VM1L5030](#)

VM1L Series LED Low Bay, Hazardous Rated 50 Watt, 120-277
VAC 5000K, 7656 Lumens

Features

L70 Values - Industry Nomenclature for Hours of use to 70% of
Initial Lumens (TM-21+ Cal.)

General

Catalog Number	VM1L5030
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lumen Range	5,001-10,000 lm
Lumens	6162
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Optic Type	Luminaire Only
Series	VM1L
UPC	783936097954

Dimensions

Weight	15.5 lb
--------	---------

Electrical Ratings



Current Rating	100 A
Frequency Rating	50/60 Hz
Lumens Per Watt	123.2
Voltage Rating	120-277 VAC
Wattage	50 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VM1L5030 Specification Sheet French](#)
- [Specifications - VM1L Series Specification Sheet](#)
- [Specifications - VM1L5030 Specification Sheet English](#)



A Hubbell brand