



DVL1330A2G - DVL Series LED Dust Tight / Utility Hazardous Rated 13 Watt, 120-277 VAC 5000K, 1144 Lumens

By Killark
Catalog # [DVL1330A2G](#)

The DVL Series is a Dust Tight/ Utility fixture using energy efficient LED's. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. With the design of this fixtures internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins.



Features

- Compact in Size with Traditional Industrial Appearance and Suitability
- DVL LED Housings can be retrofitted to existing DV Series splice boxes to upgrade from incandescent housing 100 Series components
- World Voltage 120 - 277VAC 50/60Hz
- Instant On - Including after power interruption
- Solder-LESS LED Board Connections - Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified "Absolute" Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)

General

| | |
|-------------------|--|
| Catalog Number | DVL1330A2G |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type | Peinture époxy en poudre |
| Light Source | |
| Lumen Range | 0-2,000 lm |
| Lumens | 1144 |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| Mounting Type | |
| Optic Type | Glass Globe - Clear |
| Series | DVL |
| UPC | 783936084114 |

Dimensions

| | |
|----------|------|
| Hub Size | 3/4" |
|----------|------|

Electrical Ratings

| | |
|------------------|-------------|
| Frequency Rating | 50/60 Hz |
| Lumens Per Watt | 88 |
| Voltage Rating | 120-277 VAC |
| Wattage | 13 W |

Certifications And Compliance

| | |
|---------------------|--|
| Hazardous Rating(s) | Class I, Division 2, Groups A, B, C, D Class II, Division 2, Groups E, F, G Class III, Divisions 1 & 2 |
|---------------------|--|

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_DVL1330xxSN](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-DVL1330A2G-SPEC-EN | REV 6/2024