



## DVL1630A2G

By Killark  
Catalog # [DVL1630A2G](#)

The DVL Series is a Dust Tight/ Utility fixture using energy efficient LED's. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. With the design of this fixtures internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins.



### Features

- Compact in Size with Traditional Industrial Appearance and Suitability
- DVL LED Housings can be retrofitted to existing DV Series splice boxes to upgrade from incandescent housing 100 Series components
- World Voltage 120 - 277VAC 50/60Hz
- Instant On - Including after power interruption
- Solder-LESS LED Board Connections - Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified "Absolute" Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)

### General

Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	0-2,000 lm
Lumens	1355
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Pendant
Optic Type	Glass Globe - Clear
Series	DVL
UPC	783936084138

### Dimensions

Hub Size	3/4"
----------	------

### Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	84.7
Voltage Rating	120-277 VAC
Wattage	16 W

### Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class II, Division 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
---------------------	--

### Product Assets

[Catalogs - Killark Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Photometry - KIL\\_DVL1630xxSN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-DVL1630A2G-SPEC-EN | REV 1/2024