



VSQ Series 30A 3P 4W Hazardous Interlocked Receptacle

By Killark
Catalog # [VSQ3034](#)

30A 3W4P VSQ Hazardous Interlocked Receptacle



*Representative Image

Features

- Compact size and footprint
- Plug Interlock Mechanism for Dead-Front construction. Switch cannot be turned “ON” without fully inserted plug. Plug cannot be removed with switch in “ON” position
- Factory Wired Receptacle (Load Side) “Off” position is padlockable for maintenance safety
- Auxiliary Contact (late-make early-break) contact rated 10 Amp, 1/3 HP at 125/250 VAC.
- Adjustable mounting lugs
- Feed-through construction
- Horsepower-rated internal switch

General

Ambient Temp. Range	• -20°C to 40 °C • (T5) -20°C to 40 °C • (T6) -20°C to 40 °C
Catalog Number	VSQ3034
Color	Battleship Gray
EU RoHS Indicator	Contact Manufacturer
Hub Pattern	Feed-Thru
Material	Aluminum
Number Of Poles	3
Receptacle Type	Mechanically Interlocked
Series	VSQ
Style	3 Pole, 4-Wire
UPC	783936833323

Dimensions

Hub Size	1"
Weight	13.31 lb

Electrical Ratings

Amperage Rating	30 A
Voltage Rating	Up to 600 V

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)

Product Assets

- [Certifications - 30A VSQ Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - 30A VSQ Series IOM K1217](#)
- [Specifications - VSQ3034 Specification Sheet French](#)
- [Specifications - VSQ3034 Specification Sheet English](#)
- [Specifications - VSQ/VSQFS Series Receptacles Specification Sheet](#)



A Hubbell brand