



# XEDS-100A - XEDS Series, 100 Amp Max, Non-Fused Disconnect Switch W/ 1 Aux Contact

By Killark  
Catalog # [XEDS-100A](#)

XEDS Series, 100 Amp Max, Non-Fused Disconnect Switch W/ 1 Aux Contact.



\*Representative Image

## Features

- External handle is vault type with standard provisions for locking in "OFF" position with up to three padlocks.
- Provisions for locking in "ON" position available as factory modification (add suffix SU40 to catalog number).
- Enclosure and external handle is cast copper-free aluminum alloy (less than 4/10 of 1%).
- Cover bolts are stainless steel.
- Eaton (Cutler Hammer) Type DS Switches.
- Two cast conduit hubs, one top and one bottom.
- Internal disconnect handle mechanism is a sliding plate mounted to the cover.

## General

EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall
Number Of Poles	3
Operating Temperature Celcius Max	40 Degree
Series	XEDS
Type	<ul style="list-style-type: none"><li>• Non-Fused Disconnect</li><li>• Non-Fused Disconnect</li></ul>
UPC	783936898094

## Dimensions

Depth	7
Height	16 in
Weight	17 lb
Width	9.125 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 VAC/250 VDC

## Conductor Related

Number Of Wires	4
-----------------	---

## Certifications and Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
Nema Rating	3R, 4, 9(E, F, G)
UL File Number	E53290

## Product Assets

[Certifications - DEDS & XEDS Series UL Certification](#)  
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-XEDS-100A-SPEC-EN | REV 1/2024