



DVL1630B2G - DVL Series LED Dust Tight / Utility Hazardous Rated 16 Watt, 120-277 VAC 5000K, 1355 Lumens

By Killark
Catalog # [DVL1630B2G](#)

The DVL Series is a Dust Tight/ Utility fixture using energy efficient LED's. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. With the design of this fixtures internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins.



Features

- Compact in Size with Traditional Industrial Appearance and Suitability
- DVL LED Housings can be retrofitted to existing DV Series splice boxes to upgrade from incandescent housing 100 Series components
- World Voltage 120 - 277VAC 50/60Hz
- Instant On - Including after power interruption
- Solder-LESS LED Board Connections - Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified "Absolute" Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)

General

Catalog Number	DVL1630B2G
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Light Source	
Lumen Range	0-2,000 lm
Lumens	1355
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Clear
Series	DVL
UPC	783936109404

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	84.7
Voltage Rating	120-277 VAC
Wattage	16 W

Certifications And Compliance

Hazardous Rating(s)	Class I, Division 2, Groups A, B, C, D Class II, Division 2, Groups E, F, G Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_DVL1630xxSN](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-DVL1630B2G-SPEC-EN | REV 6/2024