



ECF-212 - 3/4" Flexible Coupling with 12" Bend Length, Bronze

By Killark
Catalog # [ECF-212](#)

3/4" Flexible Coupling with 12" Bend Length, Bronze



Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory

Application

For use in hazardous areas where movement or vibration requires a flexible connection or a difficult bend is required in a conduit system.

Specifications

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class I, Zones 1 & 2, Groups IIC, IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
---------------------	---

EU RoHS Indicator
UL File Number
CSA File Number

Contact Manufacturer
E10514
LR11716

Dimensions

Gross Weight with Packaging	2.9
Hub Size	3/4"
Width	2.625 in
Height	2.625 in
Length	18 in
Dimensions	18 in x 2.625 in x 2.625 in

General

Type	Flexible Coupling
Series	ECF Series
Material	Bronze
Finish Type	Natural
UPC	783936105154
Color	Bronze

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)