



## ESXA120AA2G

By Killark  
Catalog # [ESXA120AA2G](#)

Class I 120V 3/4" Pendant Strobe with Guard.



### Features

- Electronic component temperature range -40°C to +55°C
- NEC temperature code, T6 (<85°C)
- Flash rate-85 flashes per minute
- Xenon type lamp
- Voltage and amperage: 12-74 VDC: Draws 1.25A avg. @ 12 VDC tapering to 0.2A avg. @ 74 VDC, .75A avg. @ 24 VDC
- 120 VAC (50/60 HZ): Draws 0.30A avg.
- 240 VAC (50/60 HZ): Draws 0.17A avg.
- Power supply output: 13 watts standard 11 watts for 12-74 VDC

### General

Finish Type	Peinture époxy en poudre
Lamp Type	Flashing
Light Source	Xenon
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Pendant
Optic Type	Glass Globe - Amber
Series	ESX
UPC	783936106243

### Dimensions

Hub Size	3/4"
----------	------

### Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120 VAC

### Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
---------------------	--

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

[Certifications - ESX Series UL Certification](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - KIL\\_ESX Series Signal Luminaire IOM\\_K1121](#)



A proud member of the Hubbell Family.