



ESXA1274X2 - 12-74V DC Amber Strobe, 3/4" Ceiling Mount

By Killark

Catalog # [ESXA1274X2](#)

12-74V DC Amber Strobe, 3/4" Ceiling Mount.



Features

- Electronic component temperature range -40°C to +55°C
- NEC temperature code, T6 (<85°C)
- Flash rate-85 flashes per minute
- Xenon type lamp
- Voltage and amperage: 12-74 VDC: Draws 1.25A avg. @ 12 VDC tapering to 0.2A avg. @ 74 VDC, .75A avg. @ 24 VDC
- 120 VAC (50/60 HZ): Draws 0.30A avg.
- 240 VAC (50/60 HZ): Draws 0.17A avg.
- Power supply output: 13 watts standard 11 watts for 12-74 VDC

General

Catalog Number	ESXA1274X2
EU RoHS Indicator	Contact Manufacturer
Finish Type	Peinture époxy en poudre
Lamp Type	Flashing
Light Source	
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Optic Type	Glass Globe - Amber
Series	ESX
UPC	783936028569

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	12-74 VDC

Certifications And Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D Class I, Zones 1 & 2, Groups IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
---------------------	---

Product Assets

- [Certifications - ESX Series UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_ESX Series Signal Luminaire IOM_K1121](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-ESXA1274X2-SPEC-EN | REV 6/2024