



EXB-FDS-0303P - EXB-FDS Series, AL Fused Disconnect Switch, Switch Rating 30 -3-Pole - Top Conduit 2", Bottom Conduit 1/2", Wire Size #14-4

By Killark
Catalog # [EXB-FDS-0303P](#)

EXB-FDS Series - Aluminum Fused Disconnect Switch - Switch Rating 30 -3-Pole - Top Conduit 2 Inch - Bottom Conduit 1/2 Inch - Wire Size #14-4

Features

- Copper-free aluminum construction, high strength, lighter in weight and corrosion resistant.
- Fewer cover bolts (no corner bolts required) reduces installation and maintenance time.
- Cover bolts are stainless steel.
- Gasketed flange with O-ring located inside the bolt circle to seal out moisture.
- Stainless steel hinges are standard.
- Switch operating handle of copper-free aluminum can be padlocked, with up to three locks, in either the "ON" or "OFF" position.
- Ductile mounting lugs adjust to irregular mounting surfaces.
- Bodies have top and bottom drilled and taped conduit entrances for power and drain/breather.
- Global applications (ATEX) Enclosures are available for global applications with "CEN" suffix.
- Assemblies that are modified to CENELEC/ATEX standards maintain their North American certifications.

Application

- EXB-NFD Series hinged cover disconnect switches are used: in locations made hazardous due to the presence of flammable gasses or vapors or ignitable dusts, fibers, and flyings
- outdoors or indoors in damp, wet, and dirty locations
- or in areas where frequent washdowns, heavy rain, or water spray routinely occurs.

General

Actuator	Handle
Catalog Number	EXB-FDS-0303P
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall
Number Of Poles	3



Operating Temperature Celcius Max	40 Degree
Series	EXB-FDS
Size	8" x 10" x 6"
Type	Aluminum Fused Disconnect Switch
UPC	783936012148

Dimensions

Depth	9.875
Dimensions	14.06 in x 12.3125 in x 14.3125 in
Gross Weight with Packaging	40
Height	14.3125 in
Length	14.06 in
Weight	48 lb
Width	12.3125 in

Electrical Ratings

Amperage Rating	30 A
Frequency Rating	60 Hz
Primary Voltage	600 VAC

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

ATEX File Number	PTB 07 ATEX 1024x
CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB+H2, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X, 7(B, C, D), 9(E, F, G)
UL File Number	E10514 / E83969 / E12379

Product Assets

[Catalogs - Killark Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Installation Manuals - EXB/LT-FDS & NFD IOM K1517](#)

[Specifications - EXB-FDS-0303P Specification Sheet French](#)

[Specifications - EXBFDS0303P Specification Sheet English](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
KILL_CA-EXBFDS0303P-SPEC-EN | REV 4/2025