



# EXH Circuit Breaker Handle,4 Pole 150 Amp Frame Breaker In 6" Deep Boxes Class I, II, III, CDEFG, UL/CSA, 316 SS Shaft, Type 4X IP66

By Killark  
Catalog # EXH1A6



\*Representative Image

EXH Series,4 Pole 150 Amp Frame Breaker In 6" Deep Boxes  
Class I, II, III, CDEFG, UL/CSA, 316 SS Shaft, Cast Alum Handle  
Type 4X IP66, Circuit Breaker Handle

### Features

- Circuit breaker handle.
- Factory or field installed in a 3/4" NPSM opening.
- Has provision for Lock-On and Lock-Off with up to three padlocks.
- Consists of an external handle mechanism with through-the-enclosure shaft, internal toggle mechanism, and universal breaker pan.
- Copper free aluminum with 316 stainless steel shaft and sprongs.
- O-ring 70 durometer nitrile.
- Extruded aluminum bodies, stainless steel pins and stainless steel hardware.

### General

Catalog Number	EXH1A6
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	EXH
UPC	783936118505

### Dimensions

Dimensions	4.5 in x 1 in x 6.5 in
------------	------------------------

Gross Weight with Packaging	3
Height	6.5 in
Length	4.5 in
Width	1 in

### Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB+H2, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
Nema Rating	3, 4, 4X
UL File Number	E150827

### Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - EXH1A6 Specification Sheet English](#)
- [Specifications - EXH1A6 Specification Sheet French](#)
- [Specifications - EXH Series Circuit Breaker Handles Specification Sheet](#)



A Hubbell brand