



EXH Series CB Handle,4 Pole 250
Amp Frame Breaker In 8" Deep
Boxes Class I, II, III, CDEFG,
UL/CSA, 316 SS Shaft, Cast Alum
Handle Type 4X IP66

By Killark
Catalog # EXH1B8

EXH Series,4 Pole 250 Amp Frame Breaker In 8" Deep Boxes
Class I, II, III, CDEFG, UL/CSA, 316 SS Shaft, Cast Alum Handle
Type 4X IP66, Circuit Breaker Handle

Features

- Circuit breaker handle.
- Factory or field installed in a 3/4" NPSM opening.
- Has provision for Lock-On and Lock-Off with up to three padlocks.
- Consists of an external handle mechanism with through-the-enclosure shaft, internal toggle mechanism, and universal breaker pan.
- Copper free aluminum with 316 stainless steel shaft and sprongs.
- O-ring 70 durometer nitrile.
- Extruded aluminum bodies, stainless steel pins and stainless steel hardware.

General

Catalog Number	EXH1B8
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	EXH
UPC	783936118536

Dimensions

Dimensions	4.5 in x 1 in x 6.5 in
------------	------------------------



*Representative Image

Gross Weight with Packaging	3.5
Height	6.5 in
Length	4.5 in
Width	1 in

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB+H2, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E150827

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - EXH1B8 Specification Sheet English](#)
- [Specifications - EXH Series Circuit Breaker Handles Specification Sheet](#)
- [Specifications - EXH1B8 Specification Sheet French](#)



A Hubbell brand