



EZL12530 - EZL LED, High Bay/Low Bay, Hazardous Rated 125W 5000K, 12720 Lumens

By Killark
Catalog # [EZL12530](#)

EZL Series LED High Bay/Low Bay, Hazardous Rated 125 Watt, 120-277 VAC 5000K, 12720 Lumens

Features

-
-
-
-
-
-
-
-
-
-
-
-
-
-
-

General

Catalog Number	EZL12530
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lumen Range	10,001-15,000 lm
Lumens	12720
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Optic Type	Glass Globe - Clear
Series	EZL



UPC783936131474

Dimensions

Weight36 lb

Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	101.8
Voltage Rating	120-277 VAC
Wattage	125 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	--

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - EZ Series Luminaries CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_EZL12530](#)
- [Specifications - EZL12530 Specification Sheet French](#)
- [Specifications - EZL Series Explosion Proof Lighting Specification Sheet](#)
- [Specifications - EZL12530 Specification Sheet English](#)