



\* Representative image

# Connector, Parallel Groove

by ANDERSON  
Catalog ID: LCU70077

Three U-Bolt Aluminum Parallel Groove Connector

## Product Details

### General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Inhibitor Loaded	No
Material	Aluminum
Material - Body	Aluminum Alloy
Material - Body Halves	Aluminum Alloy
Material - Bolt	Aluminum Alloy
Material - Bottom Member	Aluminum Alloy
Material - Casting	Aluminum Alloy
Material - Hardware	Aluminum Alloy
Material - Spacer	Aluminum Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Three U-Bolt
UPC	096359320333

### Dimensions

Bolt Diameter	0.750 in
Diameter - Bolt	0.75 in
Weight	6.370 lb

### Conductor Related

Conductor Compatibility	ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Mallard-795-30/19;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61;AAC-Columbine-1351.5-61;ACAR-1024.5-30/7;ACAR-1081-18/19;ACAR-1109-30/7;ACAR-1172-30/7;ACAR-1172-18/19;ACAR-1197-30/7
Conductor Diameter (Tap) - Maximum	1.34 in

Conductor Diameter (Tap) - Minimum	1.14 in
Conductor Diameter - Maximum	1.34 in
Conductor Diameter - Minimum	1.14 in
Conductor Diameter Range	1.14 - 1.34

### Certifications and Compliance

UL Listed	No
-----------	----

### Logistics

Pallet Quantity	180 EA
-----------------	--------

**For further technical assistance, please contact us**

#### **Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### **International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)