



GECXT-3 - 1" GEC Outlet Body X Type

By Killark
Catalog # [GECXT-3](#)

1" GEC Outlet Body X Type



*Representative Image

Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

General

| | |
|-------------------|--|
| Catalog Number | GECXT-3 |
| EU RoHS Indicator | Contact Manufacturer |
| Finish Type | Powder Epoxy Paint |
| Hub Pattern | X |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| Series | GE |
| UPC | 783936210162 |

Dimensions

| | |
|-----------------------------|--------------------------|
| Dimensions | 6.25 in x 6 in x 4.25 in |
| Gross Weight with Packaging | 2.03 |
| Height | 4.25 in |
| Hub Size | 1" |
| Length | 6.25 in |
| Width | 6 in |

Certifications And Compliance

| | |
|---------------------|---|
| CSA File Number | LR11716 |
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA |
| UL File Number | E10514 |

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - GEC Series CSA Certificate of Compliance](#)
- [Certifications - GE Series Outlet Boxes ATEX Certificate](#)
- [Certifications - GEC Series Luminaire Fittings UL Certification](#)
- [Certifications - GE Series Outlet Bodies UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_GEC Series Outlet Bodies IOM_K1457](#)
- [Specifications - GECXT3 Specification Sheet English](#)
- [Specifications - GE/GEB Series Outlet Bodies Specification Sheet](#)
- [Specifications - GECXT-3 Specification Sheet French](#)



A Hubbell brand