



GOB3-A23C N34CN

By Killark
Catalog # [GOB3-A23C N34CN](#)

G Series - Aluminum ATEX Certified Long 120V Pilot Light Operator -Amber Lens With Blank Nameplate.



Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

General

Actuator	Pilot Light
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Color	<ul style="list-style-type: none"> • Amber • Amber
EU RoHS Indicator	Contact Manufacturer
Operating Cycles	10,000 hrs
Series	GO
Type	<ul style="list-style-type: none"> • Indicator • Indicator
UPC	783936225449

Dimensions

Depth	2-3/4
Gross Weight with Packaging	0.5

Electrical Ratings

Amperage Rating	0.025 A
Frequency Rating	50/60 Hz
Voltage Rating	250 V

Certifications and Compliance

ATEX File Number	03ATEX 1203 U
CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2

Nema Rating	3, 4, 4X
UL File Number	E12379

Product Assets

- [Certifications - GO Series Pilot Lights ATEX Certificate](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Certifications - GO Series Pilotlights Attestation of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.