

LED-35W Series

Off-line Switch Mode LED Drivers



Electrical Specifications Input Voltage Range: 100-277 Vac Nom. (90-305 V Min/Max) Can endure 320Vac for 48 Hrs, Input Over-Voltage: 350Vac for 2 Hrs Frequency: 50/60 Hz Nom. (47-63 Hz Min/Max) Power Factor: Inrush Current:

>0.90 @ >70% load, 120-277Vac <10.0 Amps @ 230 Vac, cold start 25°C 0.37 A @ 120Vac, full load Input Current: Maximum Power: 35W **Current Regulation:** ± 2% Over input line variation ± 4% Load Regulation: ≤ 20% @ >70% load, 120-277Vac

Leakage Current: $400~\mu A$ Typical <1S full output Start-up Time: Half Cycle Hold Up Time:

Protections

Over-voltage Output Over-current Output **Short Circuit Auto Recovery**

Environmental Specifications

Max Case Life Temp: (5 year warranty)	66°C	
Maximum Case Temp (UL):	90°C	
Minimum Starting Temp:	-30°C	
Storage Temperature:	-40°C to +85°C	
Humidity:	5% to 95%	
Cooling:	Convection	
Vibration Frequency:	5 to 55 Hz/2g, 30 minutes	
Sound Rating:	Class A	
Impact Resistance:	1g/s	
MTBF:	482,000 Hours @ full load and 40°C ambient conditions per MIL-217F Notice 2	
EMC:	FCC 47CFR Part 15 Class B compliant	
Weight:	8.8 oz (250 grams) typical	

• Total Power: 35 Watts

• Input Voltage: 100-277 Vac Nom.

- Narrow cross-section fits T5-style ballast channels
- Constant Current or Constant Voltage, with Isolation
- Black Magic Thermal Advantage[™] Plastic Housing
- UL Dry & Damp Location Rated
- IP66 & NEMA4
- Fully Encapsulated
- · High Power Factor
- Designed to be DLC & Energy Star Compliant

Note:

LED drivers are designed and intended to operate LED loads only. Non-LED loading may be outside the specified design limits of our LED drivers, and therefore cannot be covered by any warranty. If you desire to use our LED drivers to operate non-LED loads please contact us to discuss compatibility.









Constant Current Models

Model	Output Current (mA ±4%)	Output Voltage Range (Vdc)	Max. Output Power (W)	Typical Efficiency
LED35W-100-C0350-XX	350	34-100	35	86%
LED35W-054-C0700-XX	700	18-54	35	86%
LED35W-036-C1050-XX	1050	18-36	35	85%
LED35W-028-C1250-XX	1250	14-28	35	84%

⁻XX indicates dimming options are available. See options below. Blank = fixed current output

Constant Voltage Models

constant voltage models				
Model	Output Current Range (mA)	Output Voltage (Vdc ±5%)	Max. Output Power (W)	Typical Efficiency
LED35W-028	313-1250	28	35	84%
LED35W-036	263-1050	36	35	85%
LED35W-054	175-700	54	35	86%
LED35W-100	88-350	100	35	86%

Class 2: US/Canada

Dimming Option:

0-10V & Resistance dimmable models include an extra two wires +Purple/-Pink on the output side. "-D" Compatible with most quality 0-10V wall dimmers. See page 3 for additional specifications.


Safety Cert.	Standard
UL/CUL	UL8750
CSA	22.2
CE	EN61347
EMC Standard	Notes
EN61000-3-2	
EN61000-3-3	Class C




LED-35W SeriesOff-line Switch Mode LED Drivers




Dimensions



Power Characteristics





Note: The area under the life-temperature curve represents where the driver has highly reliable operation within specification. Driver performance may drift out of published specifications as the hours of operation exceed the curve at a given temperature. Higher operating temperatures increase the chances of a failure to function. Other electrical, mechanical and environmental factors affect driver lifetime but are not represented in this calculation.






LED-35W Series






"-D" Option: 0-10VDC and Resistance Dimming

Parameters	Minimum	Typical	Maximum
Source Current out of 0-10V Purple Wire	0 mA	_	0.5 mA
Absolute Voltage Range on 0-10V (+) Purple Wire	-2.0 V	_	+15 V



(Dimmer must be current-sink type control)



Notes:

- 1. 0-10V dimmable version comes with an extra two wires +Purple/-Pink on the output side.
- 2. Compatible with most 0-10V Wall Slide dimmers and direct 0-10V analog signal. Recommended dimmer is Leviton IP710 or equivalent
- 3. 0-10V dimmable version output will be $\leq 10\%$ @ 0-1.0V
- $4. \ \ \, 0\text{-}10V \ dimmable \ version \ output \ will be \ \overline{100\%} \ with \ Purple/Pink \ open \ and \ minimum \ with \ Purple/Pink \ Shorted.$
- 5. For units manufactured before Date of January 1st 2022, the Dim(-) wire will be gray, not pink.