

LTC-3RDW

LITEISTRY 3" ROUND CYLINDER

FEATURES

- 3" architectural LED downlight and wall wash cylinder delivering 600 - 2000 lm
- 4 beam distributions from 0.4 to 1.1 Spacing Criteria
- Quiet reflector appearance with 50° optical cutoff
- 2700K - 5000K, 80+ and 90+ CRI options
- Available in Surface, Wall, Pendant, or Cord Mount configurations
- Variety of dimming protocol options including 0-10V, DALI, DMX, Lutron Forward Phase and EcoSystem



CONTROL TECHNOLOGY



SPECIFICATIONS

CONSTRUCTION

- Seamless heavy gauge aluminum cylinder body with a clean appearance
- Select from 4 durable powder coat paint architectural finishes or Brushed Aluminum
- Available in Surface, Wall, Pendant, or Cable/Cord mounting options
- Wall Mount: One piece die cast aluminum mounting arm
- Wall Mount driver is integral in cylinder
- For S, CM, P: Drivers are remote mounted above ceiling (see line art)
- Pendant Mount: Swivel canopy allows sloped ceiling mounting up to 45°
- Integral driver versions allow direct mounting to a standard 4" octagonal or square junction box

OPTICS

- Visually pleasing 50° cutoff to source and source image
- The light distribution is free of distracting bright spots or pixelation and the perimeter has a smooth transition
- Optical grade silicone lens integral to light engine
- High purity spun aluminum reflector, self-flanged
- Large selection of anodized finishes and colors
- Painted cones and flange options available

ELECTRICAL

- Chip-on-board LED with 2 SDCM
- Multiple CCTs, 80+ or 90+ CRI
- Long LED life: L90 at >55,000 (TM-21)
- Universal voltage 120V-277V driver, 347V optional
- UL Class 2, inherent short circuit and overload protection, RoHS compliant
- Flicker free 0-10V dimming with 1% or <1% performance
- DALI, DMX, and Lutron Forward Phase and EcoSystem options

INSTALLATION

- Light Engine/Trim assembly is mechanically secured and includes a retention cable for ease of installation
- A quick connect is provided for easy maintenance or upgrade
- Remote mount driver/jbox assembly requires 6" plenum clearance
- Remote driver is accessible from above or below the ceiling

CERTIFICATIONS

- cCSAus certified to UL 1598
- Wall Mount: Suitable for wet locations
- Pendant Mount: Suitable for wet locations under covered ceiling
- Surface, Cord Mount and all Wall Wash: Suitable for damp locations
- This product qualifies as a "designated country construction material" per FAR 52.225-11 Buy American-Construction. Materials under Trade Agreements effective 6/6/2020. See [Buy American Solutions](#).

WARRANTY

- 5 year warranty
- See [HLI Standard Warranty](#) for additional information



RELATED PRODUCTS

Ø 3" LITEISTRY Family

Ø 4" LITEISTRY Family

Ø 6" LITEISTRY Family

KEY DATA	
Lumen Range	600-2000
Wattage Range	8-25
Efficacy Range (LPW)	80-86*
Reported Life (Hours)	L90 / >55,000
Input Current (mA)	67-208 (120V)

*Based on Specular, 35K, 80 CRI



LTC-3RDW

LITEISTRY 3" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

ORDERING GUIDE

Example: LTC-3RD-P-15L35K9WD-DM1-SS-WH

CATALOG #

LTC-3RD						
Aperture/Shape/Function	Cylinder Mounting	Lumen Output	CCT	CRI	Distribution	
LTC-3RD 3" Round Downlight Cylinder	S Surface	06L 600 Lumens	27K 2700K	8 80+ CRI	NR Narrow (0.4 SC)	
LTC-3RW 3" Round Wall Wash Cylinder	W Wall	10L 1000 Lumens	30K 3000K	9 90+ CRI	MD Medium (0.7 SC)	
	P Pendant (18" Stem Standard)	15L 1500 Lumens	35K 3500K		WD Wide (1.0 SC)	
	CM Cable/Cord (6 ft. Cord Standard) ⁵	20L 2000 Lumens	40K 4000K		XW Extra Wide (1.1 SC)	
			50K 5000K ¹		WW Wall Wash	

Driver Options	Control Options	Voltage	Reflector Finish	Reflector Color	Flange Color Options
DM1 0-10V Dimming to 1% ³	NXE NX Enabled, Dual SmartPorts ^{2,3,7}	Standard 120-277V	Finish not applicable with painted reflectors (WC or BC)	Standard Clear	Standard matches reflector color
DM01 0-10V Dimming to <1% ³			S Specular	CG Champagne Gold	WT White Flange ⁴
DMX DMX with RDM dimming to <0.1% ³	NXWE NX Wireless Enabled ^{2,3,7}	34 347V ^{3,6}	SS Semi-Specular	BL Black	BT Black Flange ⁴
DALI DALI Dimming to 1% ³	NXWD NX Wireless Enabled, Dual SmartPorts ^{2,3,7}		MFC American Matte™	LW Light Wheat	
2DM Lutron Hi-Lume 2-wire Dimming to 1% (120V Forward Phase only) ³	LV Lutron Vive Enabled, 0-10V (requires DM1 driver) ^{3,7}		VS Softglow®	PW Pewter	
EDM Lutron Hi-Lume EcoSystem Dimming to 1% ³	LVE Lutron Vive Enabled, EcoSystem, (requires EDM) ^{3,7}		VSS SoftSheen™	WC Painted White Cone and Flange	
				BC Painted Black Cone and Flange	

Exterior Cylinder Color

BA	Brushed Aluminum
BZ	Bronze
BL	Matte Black
WH	Matte White
SVR	Silver

Notes:

- 5000K available in 80+ CRI only.
- NX requires DM1 driver option.
- For lumen outputs/configurations available, see chart on page 3.
- WT not needed for WC, BT not needed for BC.
- CM standard cord color is Clear.
- 347V requires DM1 driver option; not available with Controls.
- Controls not available with wall mount (W).



LTC-3RDW

LITEISTRY 3" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

DRIVER/CONTROL OPTION AVAILABILITY

Driver and Control options listed below are available in the configurations and lumen packages as shown.

Driver/Control Option		Cylinder Mounting ¹	Integral Remote Driver ¹	06L	10L	15L	20L
DM1	0-10V 1%	W	Integral	●	●	●	●
		S/P/CM	Remote (IC Rated)	●	●	●	●
DM01	0-10V <1%	W	Integral	●	●	●	●
		S/P/CM	Remote (Non-IC)	●	●	●	
DALI	DALI 1%	W	Integral	●	●	●	●
		S/P/CM	Remote (Non-IC)	●	●	●	
DMX	DMX w/ RDM <0.1%	W	Integral		●	●	●
		S/P/CM	Remote (IC Rated)		●	●	
2DM	Lutron Hi-Lume 2-wire 1%	W	Integral		●	●	
		S/P/CM	Remote (Non-IC)		●	●	●
EDM	Lutron Hi-Lume EcoSystem 1%	W	Integral		●	●	●
		S/P/CM	Remote (Non-IC)		●	●	●
347V ³	347 Volts (DM1 required)	W	Integral		●	●	●
		S/P/CM	Remote (IC Rated)		●	●	●

NX (All)	NX (DM1 required)	W	N/A				
		S/P/CM	Remote (Non-IC)	●	●	●	●
LV	Lutron Vive® (DM1 required)	W	N/A				
		S/P/CM	Remote (IC Rated)	●	●	●	●
LVE	Lutron Vive® (EDM required)	W	N/A				
		S/P/CM	Remote (Non-IC)		●	●	●

- 1 See Cylinder Mounting chart for details.
- 2 See line art for more details.
- 3 Not available with Controls.

Cylinder Mounting	
W	Wall Mount
S	Surface Mount
CM	Cable/Cord Mount
P	Pendant Mount

CONTROLS

NX Distributed Intelligence™ Lighting Controls:

Supports applications in a variety of deployment options- wired, wireless, hybrid. Integrates with and enables a wide array of luminaires including those with SpectraSync™ Color Tuning Technology.



NX INTEGRATED CONTROLS REFERENCE								
NX Option	Sensor	Networkable	Scheduling	Occupancy	Daylight Harvesting	0-10V Dimming	On/off Control	Bluetooth® App Programming
NX Networked – Wired								
NXE	N/A	Yes	Yes	No	No	Yes	Yes	Requires NXBTC/R ¹
NX Networked – Wireless								
NXWE ²	N/A	Yes	Yes	No	No	Yes	Yes	No ³
NX Networked – Wired/Wireless								
NXWD	N/A	Yes	Yes	No	No	Yes	Yes	Requires NXBTC/R ^{1,3}

- 1 NXBTC/R needs to be plugged into an available NX SmartPort™ on the fixture network
- 2 Programming via App requires factory assistance
- 3 To program NXWE option, need to consult factory. If connected to an area controller, programming can be done from that




LTC-3RDW


LITEISTRY 3" ROUND CYLINDER

DIMENSIONS


DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	




Surface



Wall



Pendant



Cord



LTC-3RDW

LITEISTRY 3" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

PHOTOMETRY

LTC-3RD-P-20L35K8NR-DM1-S-BL


LUMINAIRE DATA

Test No.	19.00506
Description	2000 lm, Narrow, 3500K, 80 CRI
Delivered Lumens	2078
Watts	24.1W
Efficacy	86.4
Mounting	Pendant
Spacing Criterion	0.4
Beam Angle FWHM	29

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	2047	98.5
0-60	2077	99.9
0-90	2078	100.0
0-180	2078	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	6859
5	5934
15	2961
25	1243
35	201
45	28
55	2
65	1
75	0
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	9292
55°	818
65°	555
75°	0
85°	0

*Candela/Square Meter

LTC-3RD-P-20L35K8MD-DM1-S-BL


LUMINAIRE DATA

Test No.	19.00507
Description	2000 lm, Medium, 3500K, 80 CRI
Delivered Lumens	1924
Watts	24.4W
Efficacy	78.8
Mounting	Pendant
Spacing Criterion	0.8
Beam Angle FWHM	53

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1869	97.1
0-60	1922	99.9
0-90	1924	100.0
0-180	1924	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	2652
5	2634
15	2406
25	1467
35	453
45	48
55	3
65	1
75	0
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	15930
55°	1227
65°	555
75°	907
85°	0

*Candela/Square Meter

LTC-3RD-P-20L35K8WD-DM1-S-BL


LUMINAIRE DATA

Test No.	19.00509
Description	2000 lm, Wide, 3500K, 80 CRI
Delivered Lumens	1963
Watts	24.4W
Efficacy	80.5
Mounting	Pendant
Spacing Criterion	1.0
Beam Angle FWHM	59

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1887	94.8
0-60	1961	99.9
0-90	1963	100.0
0-180	1963	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	1950
5	1972
15	2062
25	1581
35	658
45	66
55	4
65	2
75	1
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	21903
55°	1636
65°	1111
75°	907
85°	0

*Candela/Square Meter

PHOTOMETRY CONTINUED

LTC-3RD-P-20L35K8XW-DM1-S-BL


LUMINAIRE DATA

Test No.	19.00508
Description	2000 lm, Extra Wide, 3500K, 80 CRI
Delivered Lumens	1942
Watts	24.4W
Efficacy	79.6
Mounting	Pendant
Spacing Criterion	1.1
Beam Angle FWHM	66

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1836	94.6
0-60	1940	99.9
0-90	1942	100.0
0-180	1942	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	1473
5	1475
15	1605
25	1545
35	890
45	76
55	4
65	2
75	1
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	21571
55°	1636
65°	1111
75°	907
85°	0

*Candela/Square Meter


LUMEN MULTIPLIER

Option	27K8	30K8	35K8	40K8	50K8	27K9	30K9	35K9	40K9
Multiplier	0.94	0.98	1.00	1.01	1.02	0.81	0.84	0.85	0.85


Photometrics are published below at a nominal 3500 Kelvin, 80+ CRI. This table may be used to approximate the lumen values at different Kelvin temperatures. Power consumption would stay the same.

TM-30 DATA

COLOR VECTOR GRAPHIC 3500K, 90 CRI




COLOR DISTORTION GRAPHIC 3500K, 90 CRI




TEST RESULTS - 3500K		
Value	80+ CRI	90+ CRI
R _i	84	88
R _g	95	95
CCT (K)	3411	3419
D _{uv}	0.0015	0.0042
x	0.4120	0.4147
y	0.3974	0.4052
CIE R _a	84	93
CIE R _g	11	62

COLOR VECTOR GRAPHIC 3500K, 80 CRI



COLOR DISTORTION GRAPHIC 3500K, 80 CRI





LTC-3RDW

LITEISTRY 3" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

ELECTRICAL DATA

DRIVER DATA		
Input Voltage	120-277 V	347 V
Input Frequency	50/60 Hz	50/60 Hz
Power Factor	≥0.90	≥0.90
THD	<20%	<20%
EMI Filtering (FCC 47 CFR Part 15)	Class A	Class A

* Values for DM1 option shown, values for other dimming options may vary.

WATTAGE DATA		
Lumen Output	Nominal Lumens	WATTAGE
06L	600	8
10L	1000	12
15L	1500	19
20L	2000	25

* Wattage may vary based on configuration and options selected

ADDITIONAL INFORMATION

DIMMING COMPATIBILITY CHART		
Dimming Driver	Manufacturer	Web Link
DM1 /DM01	Lutron DDTV	http://bit.ly/1lJvZg
DM1	Leviton AWRMG-7xx, AWSMG-7xx, AWSMT-7xx	http://bit.ly/1BJn2R9
EDM	Lutron	http://bit.ly/1vtjHAI
2DM	Lutron	http://bit.ly/1S4WjXK

DMX

See instruction sheet on www.prescolite.com for connection & installation information.

Central Inverters

For full fixture output in back-up mode, we recommend you visit www.dual-lite.com for your Central Lighting Inverter options. Please contact your local Hubbell representative for any assistance with proper sizing and loading of your inverter selection. Central lighting inverters must be ordered separately.

LiteGear: www.dual-lite.com/products/litegear_lg_series

LPS Series: www.dual-lite.com/products/lps

ENERGY STAR® Certified Models

For a list of certified models, click on the ENERGY STAR® MODELS link or visit www.energystar.gov.