



GOB3-A23C N34LEDCN

By Killark
Catalog # [GOB3-A23C N34LEDCN](#)

G Series - Aluminum ATEX Certified Long 110V LED Pilot Light
Operator -Amber Lens With Blank Nameplate

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

General

Actuator	Pilot Light
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GOB3-A23C N34LEDCN
Color	Amber
EU RoHS Indicator	Contact Manufacturer
Operating Cycles	10,000 hrs
Series	GO
UPC	783936225456

Dimensions

Depth	2-3/4
Gross Weight with Packaging	0.5

Electrical Ratings

Amperage Rating	0.025 A
-----------------	---------



Oh No!
IMAGE COMING SOON

Frequency Rating	50/60 Hz
Voltage Rating	250 V

Certifications And Compliance

ATEX File Number	03ATEX 1203 U
CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E12379

Product Assets

- [Certifications - GO Series Pilotlights Attestation of Conformity](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Certifications - GO Series Pilot Lights ATEX Certificate](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - G Series Pilot Lights Specification Sheet](#)
- [Specifications - GOB3A23CN34LEDCN Specification Sheet English](#)
- [Specifications - GOB3-A23C N34LEDCN Specification Sheet French](#)



A Hubbell brand