



G Series Extended Fifteen-Turn Potentiometer/Rheostat Operator

By Killark
Catalog # [GOL114](#)

Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.

Features

-
-
-
-

General

Action	Rotary
Actuator	Potentiometer Operator
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GOL114
Color	Black
EU RoHS Indicator	Contact Manufacturer
Series	GO
UPC	783936226613

Dimensions

Dimensions	6.31 in x 2.25 in x 1.25 in
Gross Weight with Packaging	0.5
Height	1.25 in
Length	6.31 in
Width	2.25 in



*Representative Image

Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E150827

Product Assets

- [Certifications - G Series Auxiliary Devices UL Certification](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_GO113, GO114, GOL113, GOL114 Series Rotary Operators IOM_K1081](#)
- [Specifications - GOL114 Specification Sheet English](#)
- [Specifications - GOL114 Specification Sheet French](#)
- [Specifications - G Series Push Buttons Specification Sheet](#)



A Hubbell brand