



G Series -ATEX Certified Extended 120V Pilot Light Operator -Frosted Lens With Blank Nameplate

By Killark
Catalog # [GOL3FCN](#)

G Series - Aluminum ATEX Certified Extended 120V Pilot Light Operator -Frosted Lens With Blank Nameplate.



*Representative Image

Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

General

Actuator	Pilot Light
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Application	
Catalog Number	GOL3FCN
Color	White
	Blanc
EU RoHS Indicator	Contact Manufacturer
Operating Cycles	10,000 hrs
Series	GO
Type	
UPC	783936225579

Dimensions

Depth	3-3/8
Dimensions	6.31 in x 2.25 in x 1.25 in
Gross Weight with Packaging	0.5
Height	1.25 in
Length	6.31 in
Width	2.25 in

Electrical Ratings

Amperage Rating	0.025 A
Frequency Rating	50/60 Hz
Voltage Rating	250 V

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E12379

Product Assets

- [Certifications - GO Series Pilot Lights ATEX Certificate](#)
- [Certifications - GO Series Pilotlights Attestation of Conformity](#)
- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-GOL3FCN-SPEC-EN | REV 6/2024