

H-HG-08

By Killark
Catalog # [H-HG-08](#)

Spartan Hinge, Iron Finish With Lowering Cam System Trade Size 1-1/2" With Two 4ft Galvanized Steel Poles.



Features

- Cam shaft design to effortlessly lower pole to serviceable level
- Retrofittable to existing stanchion poles, no need to replace any conduit runs
- Certified and tested up to 250mph wind speeds
- Available in AL, SS and FE
- Conduit pole slips in between an outer an inner lip with a weep hole allowing for Type 3R ratings
- Complete and customizable solutions including lighting, fittings, and conduit

Application

For luminaires and other electrical devices mounted on poles in industrial walkways, platforms, stairwells or anywhere OSHA/HSE regulations would require fall prevention equipment. For safe and easy service to existing or new installation of stanchion poles.

General

Finish Type	Natural
Material	Iron
Series	Spartan Pole
Type	<ul style="list-style-type: none">• Pole Assistance• Pole Assistance
UPC	783936184234

Dimensions

Height	102 in
Hub Size	1-1/2"
Weight	18.83 lb
Width	4.95 in

Product Assets

- [3D Product View](#)
- [Brochures - Spartan Pole Series - A New Lighting Retrieval Solution](#)
- [Certifications - Spartan Pole Series UL Certificate of Compliance](#)
- [Installation Manuals - Spartan Pole Series Retrofit](#)
- [Video - Spartan Pole Introduction](#)