



H-SS-10 - Spartan Hinge, Stainless Steel Finish With Lowering Cam System Trade Size 1-1/2" With One 4ft & 6ft Stainless Steel Poles

By Killark
Catalog # [H-SS-10](#)



Spartan Hinge, Stainless Steel Finish With Lowering Cam System
Trade Size 1-1/2" With One 4ft & 6ft Stainless Steel Poles.

Features

- Cam shaft design to effortlessly lower pole to serviceable level
- Retrofittable to existing stanchion poles, no need to replace any conduit runs
- Certified and tested up to 250mph wind speeds
- Available in AL, SS and FE
- Conduit pole slips in between an outer an inner lip with a weep hole allowing for Type 3R ratings
- Complete and customizable solutions including lighting, fittings, and conduit

General

Application	
Catalog Number	H-SS-10
Finish Type	Naturel
Material	316 Stainless Steel
Series	Spartan Pole
Type	
UPC	783936184258

Dimensions

Height	126 in
Hub Size	1-1/2"
Weight	37 lb
Width	4.95 in

Product Assets

- [3D Product View - Spartan](#)
- [Brochures - Spartan Pole Series - A New Lighting Retrieval Solution](#)
- [Certifications - Spartan Pole Series UL Certificate of Compliance](#)
- [Installation Manuals - Spartan Pole Series Retrofit](#)
- [Video - Spartan Pole Introduction](#)



A Hubbell brand