




Aluminum Drain, M20 - Ex e Class I Div. 2 IP66/4X

By Killark
Catalog # [KDEALOM20](#)

Aluminum Drain, M20 - Ex e Class I Div. 2 IP66/4X.



*Representative Image

Features

- Silicone O-ring supplied as standard and suitable for use in a -55°C to +80°C temperature range.
- Aluminum.
- Internal 316 stainless steel locknut supplied as standard.
- When tightened to the proper torque the joint makes a hose down tight seal for type 4, 4X & IP66 application.

General

Application	
Catalog Number	KDEALOM20
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Celcius Max	80
Operating Temperature Celcius Min	-55 °C
Operating Temperature Range Celcius	-55°C to 80°C
Series	KDE
Type	
UPC	783936121673

Dimensions

Hub Size	M20
----------	-----

Certifications And Compliance

ATEX File Number	15ATEX3028X
CSA File Number	2715851
Hazardous Rating(s)	Class I, Divisions 2, Groups A, B, C, D Class I, Zones 1 & 2 Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
IECEX File Number	15.0002X
Nema Rating	3, 4, 4X

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - KDE Series CSA Certification](#)
- [Certifications - KDE Series Drain Breathers IECEx Certification](#)
- [Certifications - KDE Series ATEX Certificate](#)
- [Certifications - KDE Series Declaration of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KDE Series IOM K1458](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-KDEALOM20-SPEC-EN | REV 6/2024