



LAL2830D - LAL LED Linear, Hazardous Rated 28W 5000K, 3321 Lumens

By Killark
Catalog # [LAL2830D](#)

LAL Series LED Linear, Hazardous Rated 28 Watt, 120-277 VAC, 5000K, 3321 Lumens

Features

L70 Values - Industry Nomenclature for Hours of use to 70% of initial Lumens - TM-21 & Calculated

General

Catalog Number	LAL2830D
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Lumen Range	2,001-5,000 lm
Lumens	3321
Material	Aluminum
Operating Temperature Celcius Max	40
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40°C to 40°C
Optic Type	Polycarbonate Lens - Diffused
Series	LAL
UPC	783936123271

Dimensions

Hub Size	3/4"
Weight	17.9 lb

Electrical Ratings

Frequency Rating	50/60 Hz
Lumens Per Watt	46.4



*Representative Image

Voltage Rating	120-277 VAC
Wattage	28 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2 • Zone 2 • Zone 21
IP Rating	IP66

Product Assets

- [3D Models - LAL Series 1 Lens 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - LAL Series Declaration of Conformity](#)
- [Certifications - LAL Series EU Type ATEX Certificate](#)
- [Certifications - LAL Series CSA Certificate Of Compliance](#)
- [Certifications - LAL Series ATEX Certificate](#)
- [Certifications - LAL Series IECEx Certification](#)
- [Certifications - LAL Series INMETRO Certificate of Conformity](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - LAL Series LED Luminaires IOM K1449](#)
- [Photometry - KIL_LAL2830D](#)
- [Specifications - LAL2830D Specification Sheet English](#)
- [Specifications - LAL2830D Specification Sheet French](#)



A Hubbell brand