



# NVSLCFG26AXG - NV2 Series, Gray Non-Metallic Compact Flashing LED Light Fixt (LED Included), 3/4" Ceiling Mount w/ Amber Strobelight & Guard, 12-80VDC

By Killark  
Catalog # [NVSLCFG26AXG](#)



NV2 Series - Gray Non-Metallic Corrosion Resistant Compact Flashing LED Light Fixture (LED Included) - 3/4 Inch Ceiling Mount With Amber Strobelight And Guard - 12-80VDC

## Features

- NVSL Series LED with very compact profile and 50,000 hours expected life steady - on or flashing.
- NVSZ Series Xenon with 10,000 hours expected life flashing only.
- LED utilizes inverted cone design to provide full 360 degree coverage for more light projection.
- LED and Xenon available in five colors colors - red, green, amber, blue and clear.
- Flash rate for LED is 7 micro flashes approximately every second for increased visual perception.
- Xenon flash rate 60 to 80 per minute
- Can be mounted in any orientation including lens in the UP or SIDE positions.
- Materials: High strength 30% glass-filled thermoset polyester body with Lexan® lens. Resists corrosive effects of most chemicals, hydrocarbons and solvents
- Designed for indoor and outdoor applications

## General

Catalog Number	NVSLCFG26AXG
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Steady
Material	Polyester, Fiberglass Reinforced
Optic Type	Polycarbonate Globe - Amber

Series	NV
UPC	783936070568

## Dimensions

Hub Size	3/4"
----------	------

## Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	12-80 VDC / 24 VAC

## Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Division 2, Groups A, B, C, D</li> <li>• Class I, Zone 2, Groups IIC, IIB, IIA</li> <li>• Class II, Division 2, Groups F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
IP Rating	IP66

## Product Assets

- [Certifications - NVSL & NVSP Series CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - NVSLCFG26AXG Specification Sheet English](#)
- [Specifications - NVSLCFG26AXG Specification Sheet French](#)
- [Specifications - NVS Series Non-Metallic Corrosive Resitant Signals Specification Sheet](#)

