



Versamate Series 150A 3 Pole 4 Wire Plug Assembly

By Killark
Catalog # [VPA15034](#)

150A 3 Pole 4 Wire Plug Assembly

Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities

General

Catalog Number	VPA15034
EU RoHS Indicator	Contact Manufacturer
Finish Type	Baked Powder
	Epoxy/Polyester Finish
Grommet Range	0.88-1.91
Material	Body-Copper-free aluminum; Contacts-Brass; Spring tensioner-Patented beryllium



Series	copper; External screws-316
Style	stainless steel
Type	VersaMate
UPC	Style II Pin & Sleeve 783936084053

Dimensions

Dimensions	10.87 in x 4.25 in x 4.25 in
Height	4.25 in
Length	10.87 in
Width	4.25 in

Electrical Ratings

Amperage Rating	150 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Conductor Related

Number Of Wires	3
-----------------	---

Product Assets

- [Certifications - 150A Versamate UL Certification](#)
- [Certifications - CSA Certificate - 150 Amp Versamate](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VPA15034 Specification Sheet English](#)
- [Specifications - VPA15034 Specification Sheet French](#)
- [Specifications - Versamate Series Receptacles Specification Sheet](#)



A Hubbell brand