



XECF-6A - XEC Series, 100 Amp Max, Circuit Breaker Enclosure Only

By Killark
Catalog # [XECF-6A](#)

XEC Series, 100 Amp Max, Circuit Breaker Enclosure Only

Features

- Rectangular bolted cover design provides for attractive, compact, uniform installations.
- Two case conduit hubs, one top and one bottom.
- Internal circuit breaker handle mechanism is a sliding plate type mounted to the cover.
- External handle is vault type with standard provisions for locking in "OFF" position with up to three padlocks.
- Provisions for locking in "ON" position as factory modification (add suffix SU40 to the catalog number).
- Circuit Breaker is trip free of handle mechanism.
- Locking in the "ON" position does not prevent the circuit breaker from opening under short circuit or overload conditions.

General

Actuator	Molded Case Circuit Breaker Operator
Catalog Number	XECF-6A
Color	Aluminum
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Finish Type	Lacquer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Celcius Max	40 Degree
Series	XEC



UPC 783936897141

Dimensions

Depth	7
Height	16 in
Weight	20 lb
Width	7.75 in

Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Certifications And Compliance

CSA File Number	LR18179
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	7 (B, C, D), 9 (E, F, G)
UL File Number	E30962

Product Assets

- [Customer Notices - Prop 65 Notice](#)
[Specifications - XEC Series Circuit Breakers Specification Sheet](#)
[Specifications - XECF-6A Specification Sheet French](#)
[Specifications - XECF6A Specification Sheet English](#)