



HCMP800TS-300 - Variable Speed Pressure Limiting Across-The-Line Bypass with Automatic Transfer Switch

By Metron/Metron-Eledyne
Catalog # [HCMP800TS-300](#)



Variable Speed Pressure Limiting Across-The-Line Bypass with Automatic Transfer Switch

Features

Service Entrance Rated

General

Application	Fire Protection System
Series	MP
Temperature Range	4.4°C to 50°C
Type	Variable Speed Pressure Limiting with ATS

Electrical Ratings

Frequency Rating	50/60 Hz
Power Factor	50-350
Voltage Rating	200-600 V

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Product Assets

- [Brochures - SERIES MP800 VFD](#)
- [Installation Manuals - METRON_MP800_Manual](#)
- [Submittal Packages - MP800-300TS Submittal Selection Table](#)