

# LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUBB™

LITEISTRY™

## FEATURES

- 3" architectural LED downlight and wall wash cylinder delivering 600–2000 lm
- Five beam distributions from 0.3 to 1.1 Spacing Criteria
- Quiet reflector appearance with 50° optical cutoff
- 2700K - 5000K, 80+ and 90+ CRI options
- Available in Surface, Wall, Pendant, or Cable/Cord Mount configurations
- Versatile canopy options for recessed and surface-mounted J-box applications
- PowerHUBB™ enables low-voltage wired connectivity for Power over Ethernet (PoE) network system deployment



(Select Models)

## RELATED PRODUCTS

Ø 3" LITEISTRY Family

Ø 4" LITEISTRY Family

Ø 6" LITEISTRY Family

## CONTROL TECHNOLOGY



## SPECIFICATIONS

### CONSTRUCTION

- Seamless heavy gauge aluminum cylinder body with a clean appearance
- Available in Surface (S), Wall (W), Pendant (P), or Cable/Cord (CM) mounting types
- Canopy options include Power Canopy (PC), Power Conduit Canopy (PCC), or Recessed Mount Driver (RMD), (See Dimensions section for details)
- For S, P, or CM mounting with PCC canopy options, use 4" octagonal junction box (by others)
- Wall Mount: Die cast aluminum mounting arm allows direct mounting to standard 4" octagonal or square junction box
- Pendant Mount canopy options allow sloped ceiling up to 35° (5° for RMD)
- Select from 4 standard architectural painted finishes, Brushed Aluminum, or specified custom color

### OPTICS

- Visually pleasing 50° cutoff to source and source image
- The light distribution is free of distracting bright spots or pixelation and the perimeter has a smooth transition
- Optical grade silicone lens integral to light engine
- High purity spun aluminum reflector, self-flanged
- Large selection of anodized finishes and colors
- Painted cones and flange options available

### ELECTRICAL

- Chip-on-board LED with 2 SDCM
- Multiple CCTs, 80+ or 90+ CRI
- Long LED life: L90 at >55,000 (TM-21)
- PowerHUBB™ enables low-voltage wired connectivity for Power over Ethernet (PoE) network system deployment
- EMI Filtering (FCC 47 CFR Part 15) Class A

### INSTALLATION

- Light Engine/Trim assembly is mechanically secured and includes a retention cable for ease of installation
- A quick connect is provided for easy maintenance or upgrade
- For Wall Mount (W): Factory supplied remote node assembly to be field installed. Access required to an appropriate indoor IP20 rated node location (by others). See Wall mount line art in Dimensions section for details.
- Recessed Mount Driver (RMD) is accessible from above or below ceiling; assembly mounts with 1/4-20 threaded rod (by others) and requires 6" plenum clearance
- Conduit Canopy options (PCC) allow field selectable conduit entry (up to 4@ 90°) (See Dimensions section)
- Conduit Canopy utilizes a patent pending mounting yoke to secure cylinder to the ceiling surface
- Cable/Cord can be cut in the field to custom length
- Standard and Custom Pendant lengths available (specify when ordering)

### CERTIFICATIONS

- cCSAus certified to UL 2108
- Wall Mount (except PCC): Suitable for wet locations
- Pendant Mount (except PCC): Suitable for wet locations under covered ceiling
- Surface, Cable/Cord Mount and PCC and all Wall Wash: Suitable for damp locations
- This product qualifies as a "designated country construction material" per FAR 52.225-11 Buy American-Construction. Materials under Trade Agreements effective 6/6/2020. See [Buy American Solutions](#).

### WARRANTY

- 5 year warranty
- See [HLI Standard Warranty](#) for additional information

| KEY DATA              |               |
|-----------------------|---------------|
| Lumen Range           | 600-2000      |
| Wattage Range         | 8-25          |
| Efficacy Range (LPW)  | 80-86*        |
| Reported Life (Hours) | L90 / >55,000 |
| Input Current (mA)    | N/A           |

\*Based on Specular, 35K, 80 CRI



# LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUBB™

|            |           |
|------------|-----------|
| DATE:      | LOCATION: |
| TYPE:      | PROJECT:  |
| CATALOG #: |           |

## ORDERING GUIDE

Example: LTC-3RDPH-CM15WHPCC-15L35K9WD-PMC-SS-WH

|           |  |
|-----------|--|
| CATALOG # |  |
|-----------|--|

| LTC-3RDPH                             |                                                                                             |                                                                                          |                                     |                               |                  |
|---------------------------------------|---------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|-------------------------------------|-------------------------------|------------------|
| Aperture/Shape/Function               | Cylinder Mounting                                                                           | Canopy Option                                                                            | Lumen Output                        | CCT                           | CRI              |
| LTC-3RDPH 3" Round Downlight Cylinder | <b>S</b> Surface                                                                            | Refer to chart on Page 3 for available canopy options based on driver/controls selection | <b>06L</b> 600 Lumens <sup>3</sup>  | <b>27K</b> 2700K              | <b>8</b> 80+ CRI |
| LTC-3RWPH 3" Round Wall Wash Cylinder | <b>W</b> Wall                                                                               |                                                                                          | <b>10L</b> 1000 Lumens <sup>3</sup> | <b>30K</b> 3000K              | <b>9</b> 90+ CRI |
|                                       | <b>P</b> Pendant (Standard)                                                                 |                                                                                          | <b>15L</b> 1500 Lumens <sup>3</sup> | <b>35K</b> 3500K              |                  |
|                                       | Nominal 18" length from cylinder top to ceiling <sup>7</sup>                                | <b>PC</b> Standard Canopy <sup>3,6</sup>                                                 | <b>20L</b> 2000 Lumens <sup>3</sup> | <b>40K</b> 4000K              |                  |
|                                       | <b>P_</b> Pendant (Custom)                                                                  | <b>PCC</b> Power Conduit Canopy <sup>3,6</sup>                                           |                                     | <b>50K</b> 5000K <sup>1</sup> |                  |
|                                       | Specify length from cylinder top to ceiling in 1 inch increments from 15 to 60 <sup>7</sup> | <b>RMD</b> Recessed Mount Driver <sup>3,6</sup>                                          |                                     |                               |                  |
|                                       | <b>Cable/Cord</b> <sup>5</sup>                                                              |                                                                                          |                                     |                               |                  |
|                                       | <b>CM</b> 6ft Clear Cord                                                                    |                                                                                          |                                     |                               |                  |
|                                       | <b>CMBL</b> 6ft Black Cord                                                                  |                                                                                          |                                     |                               |                  |
|                                       | <b>CMWH</b> 6ft White Cord                                                                  |                                                                                          |                                     |                               |                  |
|                                       | <b>CM15</b> 15ft Clear Cord                                                                 |                                                                                          |                                     |                               |                  |
|                                       | <b>CM15BL</b> 15ft Black Cord                                                               |                                                                                          |                                     |                               |                  |
|                                       | <b>CM15WH</b> 15ft White Cord                                                               |                                                                                          |                                     |                               |                  |

| Distribution                                     | PowerHUBB Node                                                  | Reflector Finish                                         | Reflector Color                         | Flange Color Options                |
|--------------------------------------------------|-----------------------------------------------------------------|----------------------------------------------------------|-----------------------------------------|-------------------------------------|
| <b>VNR</b> Very Narrow (0.3 SC/20°) <sup>5</sup> | <b>PM</b> PowerHUBB™, On/Off/1% Dim, Master                     | Finish not applicable with painted reflectors (WC or BC) | Standard Clear                          | Standard matches reflector color    |
| <b>NR</b> Narrow (0.4 SC/29°)                    | <b>PMC</b> PowerHUBB™, On/Off/1% Dim, Control Inputs, Master    | <b>S</b> Specular                                        | <b>CG</b> Champagne Gold                | <b>WT</b> White Flange <sup>2</sup> |
| <b>MD</b> Medium (0.7 SC/53°)                    | <b>PS</b> PowerHUBB™, On/Off/1% Dim, Satellite                  | <b>SS</b> Semi-Specular                                  | <b>BL</b> Black                         | <b>BT</b> Black Flange <sup>2</sup> |
| <b>WD</b> Wide (1.0 SC/59°)                      | <b>PSC</b> PowerHUBB™, On/Off/1% Dim, Control Inputs, Satellite | <b>MFC</b> American Matte™                               | <b>LW</b> Light Wheat                   |                                     |
| <b>XW</b> Extra Wide (1.1 SC/66°)                |                                                                 | <b>VS</b> Softglow®                                      | <b>PW</b> Pewter                        |                                     |
| <b>WW</b> Wall Wash                              |                                                                 | <b>VSS</b> SoftSheen™                                    | <b>WC</b> Painted White Cone and Flange |                                     |
|                                                  |                                                                 |                                                          | <b>BC</b> Painted Black Cone and Flange |                                     |

| Exterior Cylinder Color                                                                                           |
|-------------------------------------------------------------------------------------------------------------------|
| <b>BA</b> Brushed Aluminum <sup>8</sup>                                                                           |
| <b>BZ</b> Bronze                                                                                                  |
| <b>BL</b> Matte Black                                                                                             |
| <b>WH</b> Matte White                                                                                             |
| <b>SVR</b> Silver                                                                                                 |
| <b>CC_</b> Custom Color (Specify RAL#, Example: CCRAL1073)                                                        |
| <b>TCC_</b> True Custom Color (Specify description, Example: TCC BABY BLUE, Paint chip must be provided to match) |

### Notes:

- 1 5000K available in 80+ CRI only.
- 2 WT not needed for WC, BT not needed for BC.
- 3 For lumen outputs/configurations available see chart on page 3.
- 4 Cable/Cord can be cut in the field to custom length.
- 5 VNR available up to 15L.
- 6 See Dimensions section for canopy configuration details.
- 7 Stem length varies by canopy configuration. See Dimensions section for details.
- 8 Canopy color for Brushed Aluminum is Black.



# LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUBB™

|            |           |
|------------|-----------|
| DATE:      | LOCATION: |
| TYPE:      | PROJECT:  |
| CATALOG #: |           |

## DRIVER/CONTROL OPTION AVAILABILITY

Driver and Control options listed below are available in the configurations and lumen packages as shown.

| Driver/Control Option |          | Cylinder Mounting <sup>1</sup> | Canopy Options <sup>2</sup> | 06L | 10L | 15L | 20L |
|-----------------------|----------|--------------------------------|-----------------------------|-----|-----|-----|-----|
| All PH                | 0-10V 5% | W                              | Standard                    | ●   | ●   | ●   | ●   |
|                       |          | W                              | PC/PCC                      | ●   | ●   | ●   | ●   |
|                       |          | P/S/CM                         | PC/PCC/RMD                  | ●   | ●   | ●   | ●   |

- 1 See Cylinder Mounting chart.  
2 See Canopy Options chart and Dimensions section for details.

| Cylinder Mounting |                  | Canopy Options |                                           |
|-------------------|------------------|----------------|-------------------------------------------|
| S                 | Surface Mount    | (Blank)        | Standard Canopy with remote node assembly |
| W                 | Wall Mount       | PC             | Power Canopy                              |
| P                 | Pendant Mount    | PCC            | Power Conduit Canopy                      |
| CM                | Cable/Cord Mount | RMD            | Recessed Mount Driver/Node                |


## PERFORMANCE DATA TABLE

Performance data provided below is for 3500K, 80 CRI with Specular Clear reflector finish/color


| Lumen Package | Nominal Lumens | Distribution          | Delivered Lumens | Watts | LPW |
|---------------|----------------|-----------------------|------------------|-------|-----|
| 06L           | 600            | Very Narrow           | 689              | 8.0   | 87  |
|               |                | Narrow                | 744              | 7.8   | 95  |
|               |                | Medium                | 641              | 7.8   | 82  |
|               |                | Wide                  | 663              | 7.8   | 85  |
|               |                | Extra Wide            | 636              | 7.8   | 82  |
|               |                | Open Single Wall Wash | 560              | 7.8   | 72  |
| 10L           | 1000           | Very Narrow           | 1099             | 12.6  | 87  |
|               |                | Narrow                | 1198             | 11.9  | 101 |
|               |                | Medium                | 1032             | 11.9  | 87  |
|               |                | Wide                  | 1067             | 11.9  | 90  |
|               |                | Extra Wide            | 1024             | 11.9  | 86  |
|               |                | Open Single Wall Wash | 901              | 11.9  | 76  |
| 15L           | 1500           | Very Narrow           | 1502             | 18.6  | 81  |
|               |                | Narrow                | 1733             | 18.6  | 93  |
|               |                | Medium                | 1493             | 18.6  | 80  |
|               |                | Wide                  | 1544             | 18.6  | 83  |
|               |                | Extra Wide            | 1482             | 18.6  | 80  |
|               |                | Open Single Wall Wash | 1304             | 18.6  | 70  |
| 20L           | 2000           | Narrow                | 2103             | 25.1  | 84  |
|               |                | Medium                | 1952             | 25.1  | 78  |
|               |                | Wide                  | 1985             | 25.1  | 79  |
|               |                | Extra Wide            | 1945             | 25.1  | 77  |
|               |                | Open Single Wall Wash | 1804             | 24.2  | 75  |

## DIMENSIONS


### SURFACE (S)



**Surface  
Recessed Mount Driver  
SRMD**




**Surface  
Power Canopy  
SPC**




**Surface  
Power Conduit Canopy  
SPCC**

## DIMENSIONS

### WALL (W)



### Wall Standard Canopy W



### Remote Node Mounting


| Lumen Package | 14 to 18 AWG Wire Size Max.<br>Wire Length* (in feet) |
|---------------|-------------------------------------------------------|
| 06L           | 460                                                   |
| 10L           | 275                                                   |
| 15L           | 180                                                   |
| 20L           | 140                                                   |

\*Measured from Node to LED module connection  
(Based on 1V drop)


### LTC3-W-PH

### Remote Node Detail

**WALL (W) (CONTINUED)**




**Wall  
Power Canopy  
WPC**




**Wall  
Power Conduit Canopy  
WPCC**

## DIMENSIONS


### CABLE/CORD (CM)



**Cable/Cord  
Recessed Mount Driver  
CMRMD**



**Cable/Cord  
Power Canopy  
CMPC**



**Cable/Cord  
Power Conduit Canopy  
CMPCC**



# LTC-3RDWPH

## LITE|STRY 3" ROUND CYLINDER WITH POWERHUBB™

|            |           |
|------------|-----------|
| DATE:      | LOCATION: |
| TYPE:      | PROJECT:  |
| CATALOG #: |           |


## DIMENSIONS

### PENDANT (P)



**DIMENSIONS**

**PENDANT CUSTOM LENGTH**



Custom Length (CL) = Mounting Height (A) - Fixture Height (B) - 7" Cylinder


Ordering Example:

A (120") - B (72") - 7" = 41" Custom Length  
LTC-3RD-P41


## DIMENSIONS

### CONDUIT CANOPY DETAILS

CC and PCC Conduit Canopy options come standard with (4) Solid Keys installed and (4) Conduit Keys provided.  
Accommodates a 4" octagonal junction box with 1-1/2" depth (by others).



### CONDUIT MOUNTING EXAMPLES - FIELD INTERCHANGEABLE





# LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUB™

|            |           |
|------------|-----------|
| DATE:      | LOCATION: |
| TYPE:      | PROJECT:  |
| CATALOG #: |           |

## PHOTOMETRY

### LTC-3RDPH-P-15L35K8VNR-PMC-S-BL


#### LUMINAIRE DATA

|                   |                                     |
|-------------------|-------------------------------------|
| Test No.          | R20.01326-C02                       |
| Description       | 1500 lm, Very Narrow, 3500K, 80 CRI |
| Delivered Lumens  | 1502                                |
| Watts             | 18.6W                               |
| Efficacy          | 81                                  |
| Mounting          | Pendant                             |
| Spacing Criterion | 0.3                                 |
| Beam Angle        | 20                                  |

#### ZONAL LUMEN SUMMARY

| Zone  | Lumens | % Luminaire |
|-------|--------|-------------|
| 0-40  | 1482   | 98.7        |
| 0-60  | 1501   | 99.9        |
| 0-90  | 1502   | 100.0       |
| 0-180 | 1502   | 100.0       |

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

| Degree | Candela |
|--------|---------|
| 0      | 6446    |
| 5      | 5271    |
| 15     | 1980    |
| 25     | 879     |
| 35     | 119     |
| 45     | 18      |
| 55     | 2       |
| 65     | 1       |
| 75     | 0       |
| 85     | 0       |
| 90     | 0       |

#### LUMINANCE DATA\*

| Vertical Angle | Average |
|----------------|---------|
| 45°            | 6078    |
| 55°            | 833     |
| 65°            | 565     |
| 75°            | 0       |
| 85°            | 0       |

\*Candela/Square Meter

### LTC-3RDPH-P-20L35K8NR-PMC-S-BL


#### LUMINAIRE DATA

|                   |                                |
|-------------------|--------------------------------|
| Test No.          | R19.00506-01                   |
| Description       | 2000 lm, Narrow, 3500K, 80 CRI |
| Delivered Lumens  | 2078                           |
| Watts             | 24.1W                          |
| Efficacy          | 86.4                           |
| Mounting          | Pendant                        |
| Spacing Criterion | 0.4                            |
| Beam Angle FWHM   | 29                             |

#### ZONAL LUMEN SUMMARY

| Zone  | Lumens | % Luminaire |
|-------|--------|-------------|
| 0-40  | 2047   | 98.5        |
| 0-60  | 2077   | 99.9        |
| 0-90  | 2078   | 100.0       |
| 0-180 | 2078   | 100.0       |

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

| Degree | Candela |
|--------|---------|
| 0      | 6859    |
| 5      | 5934    |
| 15     | 2961    |
| 25     | 1243    |
| 35     | 201     |
| 45     | 28      |
| 55     | 2       |
| 65     | 1       |
| 75     | 0       |
| 85     | 0       |
| 90     | 0       |

#### LUMINANCE DATA\*

| Vertical Angle | Average |
|----------------|---------|
| 45°            | 9292    |
| 55°            | 818     |
| 65°            | 555     |
| 75°            | 0       |
| 85°            | 0       |

\*Candela/Square Meter

### LTC-3RDPH-P-20L35K8MD-PMC-S-BL


#### LUMINAIRE DATA

|                   |                                |
|-------------------|--------------------------------|
| Test No.          | R19.00507-01                   |
| Description       | 2000 lm, Medium, 3500K, 80 CRI |
| Delivered Lumens  | 1924                           |
| Watts             | 24.4W                          |
| Efficacy          | 78.8                           |
| Mounting          | Pendant                        |
| Spacing Criterion | 0.7                            |
| Beam Angle FWHM   | 53                             |

#### ZONAL LUMEN SUMMARY

| Zone  | Lumens | % Luminaire |
|-------|--------|-------------|
| 0-40  | 1869   | 97.1        |
| 0-60  | 1922   | 99.9        |
| 0-90  | 1924   | 100.0       |
| 0-180 | 1924   | 100.0       |

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

| Degree | Candela |
|--------|---------|
| 0      | 2652    |
| 5      | 2634    |
| 15     | 2406    |
| 25     | 1467    |
| 35     | 453     |
| 45     | 48      |
| 55     | 3       |
| 65     | 1       |
| 75     | 0       |
| 85     | 0       |
| 90     | 0       |

#### LUMINANCE DATA\*

| Vertical Angle | Average |
|----------------|---------|
| 45°            | 15930   |
| 55°            | 1227    |
| 65°            | 555     |
| 75°            | 907     |
| 85°            | 0       |

\*Candela/Square Meter

# LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUB™

|            |           |
|------------|-----------|
| DATE:      | LOCATION: |
| TYPE:      | PROJECT:  |
| CATALOG #: |           |

## PHOTOMETRY CONTINUED

### LTC-3RDPH-P-20L35K8WD-PMC-S-BL


#### LUMINAIRE DATA

|                   |                              |
|-------------------|------------------------------|
| Test No.          | R19.00509-01                 |
| Description       | 2000 lm, Wide, 3500K, 80 CRI |
| Delivered Lumens  | 1963                         |
| Watts             | 24.4W                        |
| Efficacy          | 80.5                         |
| Mounting          | Pendant                      |
| Spacing Criterion | 1.0                          |
| Beam Angle FWHM   | 59                           |

#### ZONAL LUMEN SUMMARY

| Zone  | Lumens | % Luminaire |
|-------|--------|-------------|
| 0-40  | 1887   | 94.8        |
| 0-60  | 1961   | 99.9        |
| 0-90  | 1963   | 100.0       |
| 0-180 | 1963   | 100.0       |

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

| Degree | Candela |
|--------|---------|
| 0      | 1950    |
| 5      | 1972    |
| 15     | 2062    |
| 25     | 1581    |
| 35     | 658     |
| 45     | 66      |
| 55     | 4       |
| 65     | 2       |
| 75     | 1       |
| 85     | 0       |
| 90     | 0       |

#### LUMINANCE DATA\*

| Vertical Angle | Average |
|----------------|---------|
| 45°            | 21903   |
| 55°            | 1636    |
| 65°            | 1111    |
| 75°            | 907     |
| 85°            | 0       |

\*Candela/Square Meter

### LTC-3RDPH-P-20L35K8XW-PMC-S-BL


#### LUMINAIRE DATA

|                   |                                    |
|-------------------|------------------------------------|
| Test No.          | R19.00508-01                       |
| Description       | 2000 lm, Extra Wide, 3500K, 80 CRI |
| Delivered Lumens  | 1942                               |
| Watts             | 24.4W                              |
| Efficacy          | 79.6                               |
| Mounting          | Pendant                            |
| Spacing Criterion | 1.1                                |
| Beam Angle FWHM   | 66                                 |

#### ZONAL LUMEN SUMMARY

| Zone  | Lumens | % Luminaire |
|-------|--------|-------------|
| 0-40  | 1836   | 94.6        |
| 0-60  | 1940   | 99.9        |
| 0-90  | 1942   | 100.0       |
| 0-180 | 1942   | 100.0       |

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

| Degree | Candela |
|--------|---------|
| 0      | 1473    |
| 5      | 1475    |
| 15     | 1605    |
| 25     | 1545    |
| 35     | 890     |
| 45     | 76      |
| 55     | 4       |
| 65     | 2       |
| 75     | 1       |
| 85     | 0       |
| 90     | 0       |

#### LUMINANCE DATA\*

| Vertical Angle | Average |
|----------------|---------|
| 45°            | 21571   |
| 55°            | 1636    |
| 65°            | 1111    |
| 75°            | 907     |
| 85°            | 0       |

\*Candela/Square Meter

#### LUMEN MULTIPLIER

| Option     | 27K8 | 30K8 | 35K8 | 40K8 | 50K8 | 27K9 | 30K9 | 35K9 | 40K9 |
|------------|------|------|------|------|------|------|------|------|------|
| Multiplier | 0.94 | 0.98 | 1.00 | 1.01 | 1.02 | 0.81 | 0.84 | 0.85 | 0.85 |

Photometrics are published below at a nominal 3500 Kelvin, 80+ CRI. This table may be used to approximate the lumen values at different Kelvin temperatures. Power consumption would stay the same.


# LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUBB™

|            |           |
|------------|-----------|
| DATE:      | LOCATION: |
| TYPE:      | PROJECT:  |
| CATALOG #: |           |

## TM-30 DATA

COLOR VECTOR GRAPHIC  
3500K, 90 CRI




— Reference Illuminant — Test Source

COLOR DISTORTION GRAPHIC  
3500K, 90 CRI



| TEST RESULTS - 3500K |         |         |
|----------------------|---------|---------|
| Value                | 80+ CRI | 90+ CRI |
| R <sub>t</sub>       | 84      | 88      |
| R <sub>g</sub>       | 95      | 95      |
| CCT (K)              | 3411    | 3419    |
| D <sub>uv</sub>      | 0.0015  | 0.0042  |
| x                    | 0.4120  | 0.4147  |
| y                    | 0.3974  | 0.4052  |
| CIE R <sub>a</sub>   | 84      | 93      |
| CIE R <sub>g</sub>   | 11      | 62      |

COLOR VECTOR GRAPHIC  
3500K, 80 CRI



— Reference Illuminant — Test Source

COLOR DISTORTION GRAPHIC  
3500K, 80 CRI



## ELECTRICAL DATA

| WATTAGE DATA |                |         |
|--------------|----------------|---------|
| Lumen Output | Nominal Lumens | WATTAGE |
| 06L          | 600            | 8       |
| 10L          | 1000           | 12      |
| 15L          | 1500           | 19      |
| 20L          | 2000           | 25      |

\* Wattage may vary based on configuration and options selected

## ADDITIONAL INFORMATION

### PowerHUBB™ POWERHUBB™ PoE LIGHTING & CONTROL

Hubbell Control Solutions' PowerHUBB™ is an enterprise-level Power over Ethernet (PoE) lighting and control platform that seamlessly integrates luminaires, sensors, user interfaces and software for a scalable intelligent building control solution.

See separate [PowerHUBB™ In-Fixture Solutions Guide](#) and [Hubbell Control Solutions PowerHUBB Brochure](#) for more details.