

LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUBB™

LITEISTRY™

FEATURES

- 3" architectural LED downlight and wall wash cylinder delivering 600–2000 lm
- 4 beam distributions from 0.4 to 1.1 Spacing Criteria
- Quiet reflector appearance with 50° optical cutoff
- 2700K - 5000K, 80+ and 90+ CRI options
- Available in Surface, Pendant, or Cord Mount configurations
- PowerHUBB™ enables low-voltage wired connectivity for Power over Ethernet (PoE) network system deployment



(Select Models)



See Certification Specifications

CONTROL TECHNOLOGY

POWERHUBB™
PoE LIGHTING & CONTROL

SPECIFICATIONS

CONSTRUCTION

- Seamless heavy gauge aluminum cylinder body with a clean appearance
- Select from 4 durable powder coat paint architectural finishes or Brushed Aluminum
- Available in Surface, Pendant, or Cable/Cord mounting options
- Drivers are remote mounted above ceiling (see line art)
- Pendant Mount: Swivel canopy allows sloped ceiling mounting up to 45°

OPTICS

- Visually pleasing 50° cutoff to source and source image
- The light distribution is free of distracting bright spots or pixelation and the perimeter has a smooth transition
- Optical grade silicone lens integral to light engine
- High purity spun aluminum reflector, self-flanged
- Large selection of anodized finishes and colors
- Painted cones and flange options available

ELECTRICAL

- Chip-on-board LED with 2 SDCM
- Multiple CCTs, 80+ or 90+ CRI
- Long LED life: L90 at >55,000 (TM-21)
- PowerHUBB™ enables low-voltage wired connectivity for Power over Ethernet (PoE) network system deployment
- EMI Filtering (FCC 47 CFR Part 15) Class A

INSTALLATION

- Light Engine/Trim assembly is mechanically secured and includes a retention cable for ease of installation
- A quick connect is provided for easy maintenance or upgrade
- Remote mount driver/jbox assembly requires 6" plenum clearance (Non-IC rated)
- Remote driver is accessible from above or below the ceiling

CERTIFICATIONS

- cCSAus certified to UL 2108
- Pendant Mount: Suitable for wet locations under covered ceiling
- Surface, Cord Mount and all Wall Wash: Suitable for damp locations
- This product qualifies as a "designated country construction material" per FAR 52.225-11 Buy American-Construction. Materials under Trade Agreements effective 6/6/2020. See [Buy American Solutions](#).

WARRANTY

- 5 year warranty
- See [HLI Standard Warranty](#) for additional information

KEY DATA	
Lumen Range	600-2000
Wattage Range	8-25
Efficacy Range (LPW)	80-86*
Reported Life (Hours)	L90 / >55,000
Input Current (mA)	N/A

*Based on Specular, 35K, 80 CRI



LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUBB™

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

ORDERING GUIDE

Example: LTC-3RDPH-P-15L35K9WD-PMC-SS-WH

CATALOG #	
-----------	--

LTC-3RDPH					
Aperture/Shape/Function	Cylinder Mounting ³	Lumen Output	CCT	CRI	Distribution
LTC-3RDPH 3" Round Downlight Cylinder	S Surface	06L 600 Lumens	27K 2700K	8 80+ CRI	NR Narrow (0.4 SC/29°)
LTC-3RWPH 3" Round Wall Wash Cylinder	P Pendant (18" Stem Standard)	10L 1000 Lumens	30K 3000K	9 90+ CRI	MD Medium (0.7 SC/53°)
	CM Cable/Cord (6 ft. Cord Standard) ⁴	15L 1500 Lumens	35K 3500K		WD Wide (1.0 SC/59°)
		20L 2000 Lumens	40K 4000K		XW Extra Wide (1.1 SC/66°)
			50K 5000K ¹		WW Wall Wash

PowerHUBB Node	Reflector Finish	Reflector Color	Flange Color Options	Exterior Cylinder Color
PM PowerHUBB™, On/Off/1% Dim, Master	<i>Finish not applicable with painted reflectors (WC or BC)</i>	<i>Standard Clear</i>	<i>Standard matches reflector color</i>	BA Brushed Aluminum
PMC PowerHUBB™, On/Off/1% Dim, Control Inputs, Master	S Specular	CG Champagne Gold	WT White Flange ²	BZ Bronze
PS PowerHUBB™, On/Off/1% Dim, Satellite	SS Semi-Specular	BL Black	BT Black Flange ²	BL Matte Black
PSC PowerHUBB™, On/Off/1% Dim, Control Inputs, Satellite	MFC American Matte™	LW Light Wheat		WH Matte White
	VS Softglow®	PW Pewter		SVR Silver
	VSS SoftSheen™	WC Painted White		
		BC Painted Black Cone and Flange		

Notes:


- 1 5000K available in 80+ CRI only.
- 2 WT not needed for WC, BT not needed for BC.
- 3 Consult factory for Wall Mount availability.
- 4 CM standard cord color is Clear.

LTC-3RDWPH


LITEISTRY 3" ROUND CYLINDER WITH POWERHUB™

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	


DIMENSIONS



Surface



Pendant



Cord



LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUB™

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

PHOTOMETRY

LTC-3RDPH-P-20L35K8NR-PMC-S-BL


LUMINAIRE DATA

Test No.	R19.00506-01
Description	2000 lm, Narrow, 3500K, 80 CRI
Delivered Lumens	2078
Watts	24.1W
Efficacy	86.4
Mounting	Pendant
Spacing Criterion	0.4
Beam Angle FWHM	29

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	2047	98.5
0-60	2077	99.9
0-90	2078	100.0
0-180	2078	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	6859
5	5934
15	2961
25	1243
35	201
45	28
55	2
65	1
75	0
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	9292
55°	818
65°	555
75°	0
85°	0

*Candela/Square Meter

LTC-3RDPH-P-20L35K8MD-PMC-S-BL


LUMINAIRE DATA

Test No.	R19.00507-01
Description	2000 lm, Medium, 3500K, 80 CRI
Delivered Lumens	1924
Watts	24.4W
Efficacy	78.8
Mounting	Pendant
Spacing Criterion	0.7
Beam Angle FWHM	53

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1869	97.1
0-60	1922	99.9
0-90	1924	100.0
0-180	1924	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	2652
5	2634
15	2406
25	1467
35	453
45	48
55	3
65	1
75	0
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	15930
55°	1227
65°	555
75°	907
85°	0

*Candela/Square Meter

LTC-3RDPH-P-20L35K8WD-PMC-S-BL


LUMINAIRE DATA

Test No.	R19.00509-01
Description	2000 lm, Wide, 3500K, 80 CRI
Delivered Lumens	1963
Watts	24.4W
Efficacy	80.5
Mounting	Pendant
Spacing Criterion	1.0
Beam Angle FWHM	59

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1887	94.8
0-60	1961	99.9
0-90	1963	100.0
0-180	1963	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	1950
5	1972
15	2062
25	1581
35	658
45	66
55	4
65	2
75	1
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	21903
55°	1636
65°	1111
75°	907
85°	0

*Candela/Square Meter

LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUB™

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

PHOTOMETRY CONTINUED

LTC-3RDPH-P-20L35K8XW-PMC-S-BL


LUMINAIRE DATA

Test No.	R19.00508-01
Description	2000 lm, Extra Wide, 3500K, 80 CRI
Delivered Lumens	1942
Watts	24.4W
Efficacy	79.6
Mounting	Pendant
Spacing Criterion	1.1
Beam Angle FWHM	66

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1836	94.6
0-60	1940	99.9
0-90	1942	100.0
0-180	1942	100.0

POLAR GRAPH



CANDELA DISTRIBUTION

Degree	Candela
0	1473
5	1475
15	1605
25	1545
35	890
45	76
55	4
65	2
75	1
85	0
90	0

LUMINANCE DATA*

Vertical Angle	Average
45°	21571
55°	1636
65°	1111
75°	907
85°	0

*Candela/Square Meter


LUMEN MULTIPLIER

Option	27K8	30K8	35K8	40K8	50K8	27K9	30K9	35K9	40K9
Multiplier	0.94	0.98	1.00	1.01	1.02	0.81	0.84	0.85	0.85

Photometrics are published below at a nominal 3500 Kelvin, 80+ CRI. This table may be used to approximate the lumen values at different Kelvin temperatures. Power consumption would stay the same.


TM-30 DATA

COLOR VECTOR GRAPHIC 3500K, 90 CRI




— Reference Illuminant — Test Source

COLOR DISTORTION GRAPHIC 3500K, 90 CRI




TEST RESULTS - 3500K		
Value	80+ CRI	90+ CRI
R _f	84	88
R _g	95	95
CCT (K)	3411	3419
D _{uv}	0.0015	0.0042
x	0.4120	0.4147
y	0.3974	0.4052
CIE R _a	84	93
CIE R _g	11	62

COLOR VECTOR GRAPHIC 3500K, 80 CRI



— Reference Illuminant — Test Source

COLOR DISTORTION GRAPHIC 3500K, 80 CRI





LTC-3RDWPH

LITEISTRY 3" ROUND CYLINDER WITH POWERHUBB™

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

ELECTRICAL DATA

WATTAGE DATA		
Lumen Output	Nominal Lumens	WATTAGE
06L	600	8
10L	1000	12
15L	1500	19
20L	2000	25

* Wattage may vary based on configuration and options selected

ADDITIONAL INFORMATION



Hubbell Control Solutions' PowerHUBB™ is an enterprise-level Power over Ethernet (PoE) lighting and control platform that seamlessly integrates luminaires, sensors, user interfaces and software for a scalable intelligent building control solution.

See separate [PowerHUBB™ In-Fixture Solutions Guide](#) and [Hubbell Control Solutions PowerHUBB Brochure](#) for more details.