

# LTC-4RDW

LITEISTRY 4" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

## FEATURES

- 4" architectural LED downlight and wall wash cylinder delivering 600–4000 lm
- 4 beam distributions from 0.4 to 1.2 Spacing Criteria
- Quiet reflector appearance with 50° optical cutoff
- 2700K–5000K, 80+ and 90+ CRI options
- Available in Surface, Wall, Pendant, or Cord Mount configurations
- Variety of dimming protocol options including 0–10V, DALI, DMX, Forward Phase and EcoSystem



(Select Models)



See Certification Specifications

## CONTROL TECHNOLOGY



## SPECIFICATIONS

### CONSTRUCTION

- Seamless heavy gauge aluminum cylinder body with a clean appearance
- Select from 4 durable powder coat paint architectural finishes or Brushed Aluminum
- Available in Surface, Wall, Pendant, or Cable/Cord mounting options
- Wall Mount: One piece die cast aluminum mounting arm
- Pendant Mount: Swivel canopy allows sloped ceiling mounting up to 45 degrees
- Integral driver versions allow direct mounting to a standard 4" octagonal or square junction box
- Some configurations require remote mount driver assembly (see line art)

### OPTICS

- Visually pleasing 50° cutoff to source and source image
- The light distribution is free of distracting bright spots or pixelation and the perimeter has a smooth transition
- Optical grade silicone lens integral to light engine
- High purity spun aluminum reflector, self-flanged
- Large selection of anodized finishes and colors
- Painted cones and flange options available

### ELECTRICAL

- Chip-on-board (COB) LED with 2 SDCM
- Multiple CCTs, 80+ or 90+ CRI
- Long LED life: L90 at 55,000 (TM-21)
- Universal voltage 120V–277V driver, 347V optional
- UL Class 2, inherent short circuit and overload protection, RoHS compliant
- Flicker free 0-10V dimming with 1% or <1% performance
- DALI, DMX, and Lutron Forward Phase and EcoSystem options

### INSTALLATION

- Light Engine/Trim assembly is mechanically secured with torsion springs for ease of installation
- A quick connect is provided for easy maintenance or upgrade
- Remote mount driver/jbox assembly requires 6" plenum clearance
- Remote driver is accessible from above or below the ceiling

### CERTIFICATIONS

- cCSAus certified to UL 1598
- Wall Mount up to 30L: Suitable for wet locations
- Pendant Mount up to 30L: Suitable for wet locations under covered ceiling
- Surface, Cord Mount, all Wall Wash, and all 35L-40L: Suitable for damp locations
- This product qualifies as a "designated country construction material" per FAR 52.225-11 Buy American-Construction. Materials under Trade Agreements effective 6/6/2020. See [Buy American Solutions](#).

### WARRANTY

- 5 year warranty
- See [HLI Standard Warranty](#) for additional information



## RELATED PRODUCTS

Ø 3" LITEISTRY Family

Ø 4" LITEISTRY Family

Ø 6" LITEISTRY Family

KEY DATA	
Lumen Range	600-4000
Wattage Range	8-52
Efficacy Range (LPW)	90-99*
Reported Life (Hours)	L90 / >55,000
Input Current (mA)	67-433 (120V)

\*Based on Specular, 35K, 80 CRI



# LTC-4RDW

LITEISTRY 4" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

## ORDERING GUIDE

Example: LTC-4RD-P-15L35K9WD-DM1-SS-WH

CATALOG #	
-----------	--

LTC-4RD					
Aperture/Shape/Function	Cylinder Mounting	Lumen Output	CCT	CRI	Distribution
LTC-4RD 4" Round Downlight Cylinder	S Surface	06L 600 Lumens	27K 2700K	8 80+ CRI	NR Narrow (0.4 SC/29°)
LTC-4RW 4" Round Wall Wash Cylinder	W Wall	10L 1000 Lumens	30K 3000K	9 90+ CRI	MD Medium (0.7 SC/44°)
	P Pendant (18" Stem Standard)	15L 1500 Lumens	35K 3500K		WD Wide (0.9 SC/61°)
	CM Cable/Cord (6 ft. Cord Standard) <sup>5</sup>	20L 2000 Lumens	40K 4000K		XW Extra Wide (1.2 SC/78°)
		25L 2500 Lumens	50K 5000K <sup>1</sup>		WW Wall Wash
		30L 3000 Lumens			
		35L 3500 Lumens <sup>8</sup>			
		40L 4000 Lumens <sup>8</sup>			

Driver Options <sup>3</sup>	Control Options	Voltage	Reflector Finish	Reflector Color	Flange Color Options
DM1 0-10V Dimming to 1% <sup>3</sup>	NXE NX Enabled, Dual SmartPorts <sup>2,3,7</sup>	Standard 120-277V	Finish not applicable with painted reflectors (WC or BC)	Standard Clear	Standard matches reflector color
DM01 0-10V Dimming to <1% <sup>3</sup>	NXWE NX Wireless Enabled <sup>2,3,7</sup>	34 347V <sup>3,6</sup>	S Specular	CG Champagne Gold	WT White Flange <sup>4</sup>
DMX DMX with RDM dimming to <0.1% <sup>3,7</sup>	NXWD NX Wireless Enabled, Dual SmartPorts <sup>3,7</sup>		SS Semi-Specular	BL Black	BT Black Flange <sup>4</sup>
DALI DALI Dimming to 1% <sup>3</sup>	LV Lutron Vive Enabled, 0-10V (requires DM1 driver) <sup>3,7</sup>		MFC American Matte™	LW Light Wheat	
2DM Lutron Hi-Lume 2-wire Dimming to 1% (120V Forward Phase only) <sup>3</sup>	LVE Lutron Vive Enabled, EcoSystem, (requires EDM) <sup>3,7</sup>		VS Softglow®	PW Pewter	
EDM Lutron Hi-Lume EcoSystem Dimming to 1% <sup>3</sup>			VSS SoftSheen™	WC Painted White Cone and Flange	
				BC Painted Black Cone and Flange	

Exterior Cylinder Color	
BA	Brushed Aluminum
BZ	Bronze
BL	Matte Black
WH	Matte White
SVR	Silver

- Notes:
- 5000K available in 80+ CRI only.
  - NX requires DM1 driver option.
  - For lumen outputs/configurations available, see chart on page 3.
  - WT not needed for WC, BT not needed for BC.
  - CM standard cord color is Clear.
  - 347V requires DM1 driver option; not available with Controls.
  - Controls not available with wall mount (W); S, P, CM with DMX or controls options require remote driver, see line art for details.
  - 35L and 40L require vented cylinder.



# LTC-4RDW

LITEISTRY 4" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

## DRIVER/CONTROL OPTION AVAILABILITY

Driver and Control options listed below are available in the configurations and lumen packages as shown.

Driver/Control Option		Cylinder Mounting <sup>1</sup>	Integral Remote Driver <sup>1</sup>	06L	10L	15L	20L	25L	30L	35L	40L
DM1	0-10V 1%	W	Integral	●	●	●	●	●	●	▼	▼
		S/P/CM	Integral	●	●	●	●	●	●	▼	▼
DM01	0-10V <1%	W	Integral	●	●	●	●	●			
		S/P/CM	Integral	●	●	●	●	●			
DALI	DALI 1%	W	Integral	●	●	●	●	●			
		S/P/CM	Integral	●	●	●	●	●			
DMX	DMX w/ RDM <0.1%	W	Integral		●	●	●	●	●		
		S/P/CM	Remote (IC Rated)		●	●					
2DM	Lutron Hi-Lume 2-wire 1%	W	Integral		●	●	●				
		S/P/CM	Integral		●	●	●				
EDM	Lutron Hi-Lume EcoSystem 1%	W	Integral		●	●	●				
		S/P/CM	Integral		●	●	●	●			
347V <sup>3</sup>	347 Volts (DM1 required)	W	Integral		●	●	●	●	●	▼	▼
		S/P/CM	Integral		●	●	●	●	●	▼	▼

NX (All)	NX (DM1 required)	W	N/A								
		S/P/CM	Remote (Non-IC)	●	●	●	●				
LV	Lutron Vive® (DM1 required)	W	N/A								
		S/P/CM	Remote (IC Rated)	●	●	●	●				
LVE	Lutron Vive® (EDM required)	W	N/A								
		S/P/CM	Remote (Non-IC)		●	●	●				

▼ Vented cylinder required, see line art for more details.

1 See Cylinder Mounting chart for details.

2 See line art for more details.

3 Not available with Controls.

Cylinder Mounting	
W	Wall Mount
S	Surface Mount
CM	Cable/Cord Mount
P	Pendant Mount

## CONTROLS

### NX Distributed Intelligence™ Lighting Controls:

Supports applications in a variety of deployment options- wired, wireless, hybrid. Integrates with and enables a wide array of luminaires including those with SpectraSync™ Color Tuning Technology.



NX INTEGRATED CONTROLS REFERENCE								
NX Option	Sensor	Networkable	Scheduling	Occupancy	Daylight Harvesting	0-10V Dimming	On/off Control	Bluetooth® App Programming
<b>NX Networked – Wired</b>								
NXE	N/A	Yes	Yes	No	No	Yes	Yes	Requires <a href="#">NXBTC/R</a> <sup>1</sup>
<b>NX Networked – Wireless</b>								
NXWE <sup>2</sup>	N/A	Yes	Yes	No	No	Yes	Yes	No <sup>3</sup>
<b>NX Networked – Wired/Wireless</b>								
NXWD	N/A	Yes	Yes	No	No	Yes	Yes	Requires <a href="#">NXBTC/R</a> <sup>1,3</sup>


1 NXBTC/R needs to be plugged into an available NX SmartPort™ on the fixture network

2 Programming via App requires factory assistance


3 To program NXWE option, need to consult factory. If connected to an area controller, programming can be done from that

**DIMENSIONS**

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	




Integral Driver




Remote Driver  
For DMX, all NX or Lutron Vive Controls

**Surface (-S)**



Integral Driver




Remote Driver  
For DMX, all NX or Lutron Vive Controls


**Pendant (-P)**

**DIMENSIONS CONTINUED**

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	




Integral Driver




Remote Driver  
For DMX, all NX or Lutron Vive Controls

Cord (-CM)



Integral Driver

Wall (-W)



Vented Detail View  
All 35L and 40L  
(All Mountings)



# LTC-4RDW

LITEISTRY 4" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

## PHOTOMETRY

### LTC-4RD-P-20L35K8NR-DM1-S-BL


#### LUMINAIRE DATA

Test No.	R19.00532-01
Description	2000 lm, Narrow, 3500K, 80 CRI
Delivered Lumens	2238
Watts	22.5W
Efficacy	99.3
Mounting	Pendant
Spacing Criterion	0.4
Beam Angle (FWHM)	29

#### ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	2208	98.6
0-60	2237	99.9
0-90	2238	100.0
0-180	2238	100.0

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

Degree	Candela
0	6877
5	6035
15	3284
25	1313
35	260
45	26
55	3
65	1
75	0
85	0
90	0

#### LUMINANCE DATA\*

Vertical Angle	Average
45°	4535
55°	645
65°	292
75°	0
85°	0

\*Candela/Square Meter

### LTC-4RD-P-20L35K8MD-DM1-S-BL


#### LUMINAIRE DATA

Test No.	R19.00533-01
Description	2000 lm, Medium, 3500K, 80 CRI
Delivered Lumens	2152
Watts	22.5W
Efficacy	95.6
Mounting	Pendant
Spacing Criterion	0.7
Beam Angle (FWHM)	44

#### ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	2113	98.2
0-60	2151	99.9
0-90	2152	100.0
0-180	2152	100.0

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

Degree	Candela
0	4053
5	3893
15	3037
25	1493
35	366
45	34
55	3
65	1
75	0
85	0
90	0

#### LUMINANCE DATA\*

Vertical Angle	Average
45°	5931
55°	645
65°	292
75°	0
85°	0

\*Candela/Square Meter

### LTC-4RD-P-20L35K8WD-DM1-S-BL


#### LUMINAIRE DATA

Test No.	R19.00534-01
Description	2000 lm, Wide, 3500K, 80 CRI
Delivered Lumens	2059
Watts	22.5W
Efficacy	91.6
Mounting	Pendant
Spacing Criterion	0.9
Beam Angle (FWHM)	61

#### ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1983	96.3
0-60	2056	99.8
0-90	2059	100.0
0-180	2059	100.0

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

Degree	Candela
0	2201
5	2210
15	2051
25	1504
35	692
45	169
55	10
65	3
75	1
85	0
90	0

#### LUMINANCE DATA\*

Vertical Angle	Average
45°	11338
55°	1075
65°	584
75°	477
85°	0

\*Candela/Square Meter

## PHOTOMETRY CONTINUED

### LTC-4RD-P-20L35K8XW-DM1-S-BL


#### LUMINAIRE DATA

Test No.	R19.00535-01
Description	2000 lm, Extra Wide, 3500K, 80 CRI
Delivered Lumens	2028
Watts	22.5W
Efficacy	90.2
Mounting	Pendant
Spacing Criterion	1.2
Beam Angle (FWHM)	78

#### ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-40	1794	88.5
0-60	2025	99.8
0-90	2028	100.0
0-180	2028	100.0

#### POLAR GRAPH



#### CANDELA DISTRIBUTION

Degree	Candela
0	1235
5	1252
15	1392
25	1454
35	1010
45	256
55	6
65	2
75	1
85	0
90	0

#### LUMINANCE DATA\*

Vertical Angle	Average
45°	44656
55°	1290
65°	584
75°	231
85°	477

\*Candela/Square Meter


#### LUMEN MULTIPLIER

Option	27K8	30K8	35K8	40K8	50K8	27K9	30K9	35K9	40K9
Multiplier	0.94	0.98	1.00	1.01	1.02	0.81	0.84	0.85	0.85

Photometrics are published below at a nominal 3500 Kelvin, 80+ CRI. This table may be used to approximate the lumen values at different Kelvin temperatures. Power consumption would stay the same.

### TM-30 DATA

#### COLOR VECTOR GRAPHIC 3500K, 90 CRI




#### COLOR DISTORTION GRAPHIC 3500K, 90 CRI



TEST RESULTS - 3500K		
Value	80+ CRI	90+ CRI
R <sub>i</sub>	84	88
R <sub>g</sub>	95	95
CCT (K)	3411	3419
D <sub>uv</sub>	0.0015	0.0042
x	0.4120	0.4147
y	0.3974	0.4052
CIE R <sub>a</sub>	84	93
CIE R <sub>g</sub>	11	62

#### COLOR VECTOR GRAPHIC 3500K, 80 CRI



#### COLOR DISTORTION GRAPHIC 3500K, 80 CRI





# LTC-4RDW

LITEISTRY 4" ROUND CYLINDER

DATE:	LOCATION:
TYPE:	PROJECT:
CATALOG #:	

## ELECTRICAL DATA

DRIVER DATA		
Input Voltage	120-277 V	347 V
Input Frequency	50/60 Hz	50/60 Hz
Power Factor	≥0.90	≥0.90
THD	<20%	<20%
EMI Filtering (FCC 47 CFR Part 15)	Class A	Class A

\* Values for DM1 option shown, values for other dimming options may vary.

WATTAGE DATA		
Lumen Output	Nominal Lumens	Wattage
06L	600	8
10L	1000	12
15L	1500	19
20L	2000	23
25L	2500	28
30L	3000	35
35L	3500	43
40L	4000	52

\* Wattage may vary based on configuration and options selected

## ADDITIONAL INFORMATION

DIMMING COMPATIBILITY CHART		
Dimming Driver	Manufacturer	Web Link
DM1 /DM01	Lutron DTVT	<a href="http://bit.ly/11jSvZg">http://bit.ly/11jSvZg</a>
DM1	Leviton AWRMG-7xx, AWSMG-7xx, AWSMT-7xx	<a href="http://bit.ly/1BJn2R9">http://bit.ly/1BJn2R9</a>
EDM	Lutron	<a href="http://bit.ly/1vtjHAI">http://bit.ly/1vtjHAI</a>
2DM	Lutron	<a href="http://bit.ly/1S4WjXK">http://bit.ly/1S4WjXK</a>

### DMX

See instruction sheet on [www.prescolite.com](http://www.prescolite.com) for connection & installation information.

### Central Inverters

For full fixture output in back-up mode, we recommend you visit [www.dual-lite.com](http://www.dual-lite.com) for your Central Lighting Inverter options. Please contact your local Hubbell representative for any assistance with proper sizing and loading of your inverter selection. Central lighting inverters must be ordered separately.

LiteGear: [www.dual-lite.com/products/litegear\\_lg\\_series](http://www.dual-lite.com/products/litegear_lg_series)

LPS Series: [www.dual-lite.com/products/lps](http://www.dual-lite.com/products/lps)

### ENERGY STAR® Certified Models

For a list of certified models, click on the ENERGY STAR® MODELS link or visit [www.energystar.gov](http://www.energystar.gov).