



## N4D7460123PT

by Wiegmann  
Catalog ID: N4D7460123PT

N4 Double Door Floor-Mount 3-Point Handle 74X60X12 Carbon Steel - Gray

### Product Details

#### General

Application	Designed to house electrical and electronic controls, components, and instruments in wet non-corrosive environments. Typical applications for these enclosures include dairies, breweries, and other food processing activities that may require hose down. Enc
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	3-Point Keylocking/Padlocking
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	12 in. high floor stand kit
Mounting Type	Floor Mount
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725865598

#### Dimensions

Cubic Capacity	40320 cu.in
Depth	24 in
Height	24 in
Weight	531 lb
Width	70 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	4
UL Listed	Yes