

**PDV-65 Optima Arrester (12.7 kV
MCOV, 7114 Hardware)**

By OHIO BRASS
Catalog # [2132637114](#)

IEEE Normal Duty Class / IEC Distribution Medium Polymer
Housed Surge Arrester

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Cantilever Bending Strength - Max.	45 Nm
Catalog Number	2132637114
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution

Dimensions

Height	10.2 in
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	23.3 in (592 mm)
Current - Low Current Long	75 A
Duration (LCLD) Test	
Duty Cycle	15 kV
Frequency Rating	48-62 Hz



MCOV	12.7 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	50.6 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 39.9 kV @ 1.5 kA• 42.5 kV @ 3 kA• 45.3 kV @ 5 kA• 51 kV @ 10 kA• 58.9 kV @ 20 kA• 73.7 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	35.7 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	15
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Lightning Surge Arresters](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Specifications - 2132637114](#)
[Specifications - Specification for IEEE Normal Duty Class Distribution Arresters](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)