

**PDV-100 Optima Arrester (7.65 kV
MCOV, 7314 Hardware)**

By OHIO BRASS
Catalog # [2137087314](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge
Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	None
Cantilever Bending Strength - Max.	80 Nm
Catalog Number	2137087314
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359411864

Dimensions

Dimensions	10.130 in x 4.560 in x 9.750 in
Height	9.75 in
Length	10.13 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	4 in (101.6 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	6 in (152.4 mm)
Stud Type	3/8-16
Weight	3.1 lb
Width	4.56 in

Electrical Ratings

Creep and Leakage Distance	14.4 in (365 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	8 kV
Frequency Rating	48-62 Hz
MCOV	7.65 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	32.7 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 23.5 kV @ 1.5 kA• 25.1 kV @ 3 kA• 26.6 kV @ 5 kA• 29 kV @ 10 kA• 32.9 kV @ 20 kA• 38.8 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	21.5 kV
Minimum Strike	5.7 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Logistics

Pallet Quantity	224
-----------------	-----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Lightning Surge Arresters](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Sales Drawings - 2137087314 \(Reference Only\)](#)



A Hubbell brand