

PDV-100 Optima Arrester (7.65 kV
MCOV, 7324 Hardware)

By OHIO BRASS
Catalog # [2137087324](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge
Arrester

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	80 Nm
Catalog Number	2137087324
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359383703

Dimensions

Dimensions	9.813 in x 8.875 in x 4.250 in
Height	4.25 in
Length	9.813 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	4 in (101.6 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to	6 in (152.4 mm)
Phase	
Stud Type	3/8-16
Weight	5.2 lb
Width	8.875 in

Electrical Ratings



*Representative Image

Creep and Leakage Distance	14.4 in (365 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	8 kV
Frequency Rating	48-62 Hz
MCOV	7.65 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	32.7 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 23.5 kV @ 1.5 kA• 25.1 kV @ 3 kA• 26.6 kV @ 5 kA• 29 kV @ 10 kA• 32.9 kV @ 20 kA• 38.8 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	21.5 kV
Minimum Strike	5.7 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
--------------------------	--

Logistics

Pallet Quantity	192
-----------------	-----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Lightning Surge Arresters](#)

Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems

Literature - Hubbell Arrester and Wildlife Guard Solution Kits

Sales Drawings - 2137087324 Drawing

Specifications - Specification for IEEE Heavy Duty Class Distribution Arresters

Specifications - 2137087324

Video - Hubbell Power Systems Metal Oxide Varistor



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
OB-2137087324-SPEC-EN | REV 3/2025