

PDV-100 Optima Arrester (15.3 kV MCOV, 7324 Hardware)

By OHIO BRASS
Catalog # 2137157324

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	80 Nm
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359383727

Dimensions

Dimensions	9.813 in x 7.313 in x 4.875 in
Height	4.875 in
Length	9.813 in
Stud Type	3/8-16
Weight	6.9 lb
Width	7.313 in

Electrical Ratings

Creep and Leakage Distance	25.2 in (640 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	18 kv
Frequency Rating	48-62 Hz
MCOV	15.3 kv
Maximum .5 Microsecond Discharge Volts @ Classifying Current	63.1 kv
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 45.6 kv @ 1.5 kA • 48.8 kv @ 3 kA • 51.7 kv @ 5 kA • 56.4 kv @ 10 kA • 64.1 kv @ 20 kA • 75.5 kv @ 40 kA
Maximum Switching Surge Protective Level @ 500A	41.7 kv
Minimum Strike	8.8 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 μs

Logistics

Pallet Quantity	112
-----------------	-----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters \(EU1587\)](#)
[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E_Catalog 70\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese \(17-5122C\)](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions \(17-5122\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French \(17-5122F\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish \(17-5122S\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Literature - Lightning Surge Arresters \(SF01023E\)](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)



A proud member of the Hubbell Family.