

PDV-100 Optima Arrester (17 kV MCOV, 7214 Hardware)

By OHIO BRASS
Catalog # 2137177214

IEEE Heavy Duty / IEC Distribution High Polymer Housed
Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	None
Cantilever Bending Strength - Max.	80 Nm
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359414193

Dimensions

Dimensions	13.063 in x 8.313 in x 5.125 in
Height	5.125 in
Length	13.063 in
Stud Type	3/8-16
Weight	4.9 lb
Width	8.313 in

Electrical Ratings

Creep and Leakage Distance	28.1 in (713 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	71.0 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 51.4 kV @ 1.5 kA • 55 kV @ 3 kA • 58.2 kV @ 5 kA • 63.5 kV @ 10 kA • 72.1 kV @ 20 kA • 85 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	47.0 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 μ s

Certifications and Compliance

Industry Standard(s)	IEEE/IEC
----------------------	----------

Logistics

Pallet Quantity	136
-----------------	-----

Product Assets

[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E_Catalog 70\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits \(SF14069E\)](#)
[Sales Drawings - 2137177214 \(Reference Only\)](#)
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
OB-213717214-SPEC-EN | REV 1/2024