


HUBBELL

Power Systems

PDV-100 Optima Arrester (17 kV MCOV, 7224 Hardware)

By OHIO BRASS
 Catalog # [2137177224](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Application	Distribution
Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	80 Nm
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359414209

Dimensions

Height	8.6 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	8.0 in (203.2 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to	10.0 in (254 mm)
Phase	
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	28.1 in (713 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond	71 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	51.4 kV @ 1.5 kA
	55 kV @ 3 kA
	58.2 kV @ 5 kA
	63.5 kV @ 10 kA
	72.1 kV @ 20 kA
	85 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	47 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	

Logistics

Pallet Quantity	112
-----------------	-----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)

[Catalogs - Arresters IEEE & IEC Distribution Class](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Spanish](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Chinese](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - French](#)

[Installation Manuals - PDV-PVR Polymer Distribution Class](#)

[Arrester Installation Instructions](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.](#)

[Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)

[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)

[Literature - Lightning Surge Arresters](#)

[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)

[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-2137177224-SPEC-EN | REV 6/2024