



# HCMP800TS-450 - Variable Speed Pressure Limiting Autotransformer Bypass with Automatic Transfer Switch

By Metron/Metron-Eledyne  
Catalog # [HCMP800TS-450](#)



Variable Speed Pressure Limiting Autotransformer Bypass with Automatic Transfer Switch

## Features

Service Entrance Rated

## General

Application	Fire Protection System
Series	MP
Temperature Range	4.4°C to 50°C
Type	Variable Speed Pressure Limiting with ATS

## Electrical Ratings

Frequency Rating	50/60 Hz
Power Factor	50-350
Voltage Rating	200-600 V

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Product Assets

- [Brochures - SERIES MP800 VFD](#)
- [Installation Manuals - METRON\\_MP800\\_Manual](#)
- [Submittal Packages - MP800-450TS Submittal Selection Table](#)