



N12604820

by Wiegmann
Catalog ID: N12604820

N12 Two Door Floor-Mount 60X48X20 Carbon Steel - Gray

Designed to protect electrical, and electronic controls, components, and instruments in typical industrial environments. Enclosure protects enclosed equipment from dust, dirt, oil, and dripping water. These enclosures are used in machine tool applications for housing motor starters, drivers, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment found in automotive, pulp and paper, wood products, textile, and similar industries.

Product Details

General

| | |
|-------------------------|--|
| Application | Designed to protect electronic controls, components and instruments in typical industrial environments from dust, dirt, oil and dripping water. These enclosures are used to machine tool applications for housing motor starters, drives, contactors, PLC's, as well as a wide variety of other electrical and electronic equipment found in automotive, pulp and paper, wood products, textile and similar industries. |
| Color | Gray |
| Construction | Continuously Welded Seams |
| Cover Type | Door |
| Finish Type | Textured |
| Latches Type | 3 Point Keylocking-Padlocking Combo |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Type | Floor Mount |
| Number of Doors (Fixed) | 2 |
| Type | Enclosure |
| UPC | 786725412051 |

Dimensions

| | |
|--------|--------|
| Depth | 20 in |
| Height | 60 in |
| Weight | 435 lb |

| | |
|-------|-------|
| Width | 48 in |
|-------|-------|

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 12 |
| UL Listed | Yes |