

# HUBBELL Power Systems

## PVI-LP Arrester (8.4 kV MCOV / Uc)

By OHIO BRASS

Catalog # [2184097334](#)

IEC Class Station Medium Polymer Housed Surge Arrester



\*Representative Image

### Features

- PVI-LP arresters comply with the latest revision of IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

### General

Application	Distribution
Bracket Type	Transformer Bracket
Color	Gray Housing
Material	ESP™ Polymer Housing
Type	Station Low

### Dimensions

Stud Type	3/8-16
-----------	--------

### Electrical Ratings

Current - Low Current Long Duration (LCLD) Test	550
Duty Cycle	10 kV
Frequency Rating	48-62 Hz
MCOV	8.4 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	28.4 kV
Maximum Discharge Voltage	22.6 kV @ 1.5 kA
	23.8 kV @ 3 kA
	24.9 kV @ 5 kA
	26.9 kV @ 10 kA
	29.8 kV @ 20 kA
	33.5 kV @ 40 kA
Pressure Relief Capability - Symmetrical rms (kA)	40
Time - Low Current Long Duration (LCLD) Test	2000 Qs
Withstand Voltage - 60 Hz Wet	22.4
Withstand Voltage - Lightning Impulse	35

### Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)

[Catalogs - Arresters IEEE & IEC Distribution Class](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)

[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)

[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)

[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)

[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
OB-2184097334-SPEC-EN | REV 6/2024