

HUBBELL Power Systems

PVI-LP Arrester (22 kV MCOV / Uc)

By OHIO BRASS

Catalog # [2184227224](#)

IEC Class Station Medium Polymer Housed Surge Arrester



*Representative Image

Features

- PVI-LP arresters comply with the latest revision of IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

General

Application	Distribution
Bracket Type	NEMA 4x5 Crossarm Bracket
Color	Gray Housing
Material	ESP™ Polymer Housing
Type	Station Low
UPC	096359671602

Dimensions

Stud Type	3/8-16
-----------	--------

Electrical Ratings

Current - Low Current Long Duration (LCLD) Test	550
Duty Cycle	27 kV
Frequency Rating	48-62 Hz
MCOV	22 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	72.4 kV
Maximum Discharge Voltage	61.4 kV @ 1.5 kA 64.9 kV @ 3 kA 67.9 kV @ 5 kA 73.2 kV @ 10 kA 81 kV @ 20 kA 91.3 kV @ 40 kA
Pressure Relief Capability - Symmetrical rms (kA)	40
Time - Low Current Long Duration (LCLD) Test	2000 Qs
Withstand Voltage - 60 Hz Wet Impulse	60.8
Withstand Voltage - Lightning Impulse	95.2

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-2184227224-SPEC-EN | REV 6/2024