

**Under-Oil Arrester (2.55 kV MCOV,
3002 Hardware)**

By OHIO BRASS
Catalog # [2211033002](#)

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge
Arrester

Features

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

Application

Under Oil

General

Catalog Number	2211033002
EU RoHS Indicator	Contact Manufacturer
Mounting Hardware	No Bracket
Mounting Type	No Bracket
UPC	096359416968

Dimensions

Length	3.71 in
--------	---------

Electrical Ratings

BIL	75 kV
Duty Cycle	3 kV
Frequency Rating	48-62 Hz



MCOV	2.55 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	10.43
Maximum Discharge Voltage	<ul style="list-style-type: none">• 8.43 kV @ 1.5 kA• 8.88 kV @ 3 kA• 9.29 kV @ 5 kA• 9.97 kV @ 10 kA• 11.04 kV @ 20 kA
Maximum Switching Surge Protective Level @ 500A	7.87

Logistics

Pallet Quantity	180
-----------------	-----

Product Assets

[Catalogs - Under Oil Arresters Catalog](#)
[Installation Manuals - Installation Instructions for Under Oil Arresters - English \(17-5144\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Sales Drawings - 2211033002](#)
[Specifications - 2211033002](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)
[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)