

**Under-Oil Arrester (5.1 kV MCOV,
3002 Hardware)**

By OHIO BRASS
Catalog # [2211053002](#)

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge
Arrester



*Representative Image

Features

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

Application

Under Oil

General

EU RoHS Indicator	Contact Manufacturer
Mounting Hardware	No Bracket
Mounting Type	No Bracket
UPC	096359416982

Dimensions

Length	5.73 in
--------	---------

Electrical Ratings

BIL	75 kV
Current Rating	2000 A
Duty Cycle	6 kV
Frequency Rating	48-62 Hz
MCOV	5.1 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	20.9
Maximum Discharge Voltage	<ul style="list-style-type: none">• 16.83 kV @ 1.5 kA• 17.72 kV @ 3 kA• 18.54 kV @ 5 kA• 19.89 kV @ 10 kA• 22.02 kV @ 20 kA
Maximum Switching Surge Protective Level @ 500A	15.69

Logistics

Pallet Quantity	360
-----------------	-----

Product Assets

[Catalogs - Under Oil Arresters Catalog \(CA01063E\)](#)
[Installation Manuals - Installation Instructions for Under Oil Arresters - English \(17-5144\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Sales Drawings - 2211053002](#)
[Video - Hubbell Power Systems In Depth: Distribution Arresters \(VI01037E0119\)](#)
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)

