



N4D626012

by Wiegmann
Catalog ID: N4D626012

N4 Double Door Floor-Mount 62X60X12 Carbon Steel - Gray

Product Details

General

Application	Designed to house electrical and electronic controls, components, and instruments in wet non-corrosive environments. Typical applications for these enclosures include dairies, breweries, and other food processing activities that may require hose down. Enc
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Door
Finish Type	Textured
Latches Type	Hasp and Staple
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	12 in. high floor stand kit
Mounting Type	Floor Mount
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725374564

Dimensions

Actual Depth	62.120 in
Actual Height	62.120 in
Actual Width	60.120 in
Cubic Capacity	230640 cu.in
Depth	62 in
Height	62 in
Weight	507 lb
Width	60 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4
UL Listed	Yes