

HUBBELL Power Systems

Under-Oil Arrester (15.3 kV MCOV, 3001 Hardware)

By OHIO BRASS
Catalog # [2211153001](#)

IEEE Heavy Duty / IEC Distribution High Under-Oil Surge
Arrester



Features

- HPS under-oil arresters comply with the latest revision of the IEEE C62.11, as well as IEC 60099-4
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

General

Application	Under Oil
EU RoHS Indicator	Contact Manufacturer
Mounting Hardware	Bracket
Mounting Type	Bracket
UPC	096359417057

Dimensions

Length	8.76 in
--------	---------

Electrical Ratings

BIL	125 kV
Current Rating	500 A
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	54.72
Maximum Discharge Voltage	50.49 kV @ 1.5 kA 53.17 kV @ 3 kA 55.62 kV @ 5 kA 59.68 kV @ 10 kA 66.06 kV @ 20 kA
Maximum Switching Surge Protective Level @ 500A	47.09

Logistics

Pallet Quantity	120
-----------------	-----

Product Assets

- [Catalogs - Under Oil Arresters Catalog](#)
- [ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 2211153001](#)
- [Video - Hubbell Power Systems In Depth: Distribution Arresters](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-2211153001-SPEC-EN | REV 6/2024