

HUBBELL Power Systems

PVR Optima (10.2 kV MCOV, 7213 Hardware)

By OHIO BRASS
Catalog # [2216107213](#)

IEEE Riser Pole Class Polymer Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Application	Distribution
Bracket Type	None
Cantilever Bending Strength - Max.	135 Nm
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359824343

Dimensions

Height	9.4 in
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	26 in (660 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	
Duty Cycle	12 kV
Frequency Rating	48-62 Hz
MCOV	10.2 kV
Maximum .5 Microsecond	36.2 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	27.8 kV @ 1.5 kA
	29 kV @ 3 kA
	30.2 kV @ 5 kA
	32.5 kV @ 10 kA
	35.9 kV @ 20 kA
	41.6 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	23.9 kV
Minimum Strike	6.1 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Product Assets

[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-2216107213-SPEC-EN | REV 6/2024